

# QUARTER-TURN SUPPLY STOP – ANGLE

## 132-G SERIES

KwikStop®

### SPECIFICATION

Sioux Chief 132 Series Quarter-Turn Supply Stops shall be used where necessary in water supply systems. Valves shall be No-Lead compliant, plated brass material with PTFE seats. Valve shall be available in 3-way or angle pattern with easy grip, oval handles. Nuts and ferrules shall be included/assembled.

### MATERIALS

**Valve body:** No lead brass<sup>1</sup>

**Ball:** Chrome-plated brass

**Ball seats:** Polytetrafluoroethylene (P.T.F.E.)

**Sleeve:** Brass

**Nut:** Brass

**Finish:** Rough brass or chrome

### WORKING LIMITS

**Maximum pressure:** 125psi / 8.6 bar

**Maximum temperature:** 160°F / 71.1°C

### DIMENSIONS

	-G1F1C	-G1Q1C	-G2C0C	-G2C1C	-G2C1C0C	-G2C1C1C
A: handle	1.812"	1.812"	1.812"	1.812"	1.812"	1.812"
B: height	1.062"	1.75"	1.75"	1.687"	1.562"	1.562"
C: length	0.875"	1.125"	1.125"	1.125"	1.125"	1.125"

	-G2C1CLH	-G2C1CN1	-G2C2C	-G2C2M	-G2F0C	-G2F1C
A: handle	1.812"	1.812"	1.812"	1.812"	1.812"	1.812"
B: height	1.625"	1.75"	1.75"	1.75"	1.5"	1.5"
C: length	1.125"	1.125"	1.125"	1.125"	1.125"	1.125"

	-G2F1C0C	-G2F1C1C	-G2F2C	-G2F2M	-G2Q1C	-G2S1C
A: handle	1.812"	1.812"	1.812"	1.812"	1.812"	1.812"
B: height	1.437"	1.437"	1.5"	1.5"	1.687"	1.812"
C: length	1.125"	1.125"	1.125"	1.125"	1.125"	1.125"

	-G2S1CE5	-G2F1C1C	-G2F2C
A: handle	1.812"	1.812"	1.812"
B: height	6.812"	1.875"	2.25"
C: length	2.25"	0.875"	0.5"


ITEM # SUBMITTED	_____
JOB NAME	_____
LOCATION	_____
ENGINEER	_____
CONTRACTOR	_____
PO#	_____ TAG _____




132-G2F1C04



132-G2F1C1C04



Angle



3-Way



### Create Item Number

## 132-G A B C D

e.g. **132-G2F1C1C**: quarter-turn 3-way supply stop, 1/2" FIP x 3/8" compression x 3/8" compression

#### INLET CONNECTION A

- 1F** = 3/8" FIP
- 1Q** = 3/8" PDQ push fit
- 2C** = 5/8" & 1/2" compression
- 2F** = 1/2" FIP
- 2Q** = 1/2" PDQ push fit
- 2S** = 1/2" female sweat
- 2V** = 1/2" CPVC
- 2X** = 1/2" PEX F1807

#### OUTLET CONNECTION B

- 0C** = 1/4" compression
- 1C** = 3/8" compression
- 2C** = 5/8" & 1/2" compression
- 2M** = 1/2" MIP

#### 2ND OUTLET CONNECTION C

- 0C** = 1/4" compression
- 1C** = 3/8" compression

#### SPECIAL OPTION D

- \_** = N/A (blank)
- LH** = loose handle
- N1** = without nut
- E5** = 5" extension w/ escutcheon

<sup>1</sup>Material is compliant with NSF-61 Annex G and California No Lead Plumbing Law

\*Not all size and length combinations available. Contact your local rep to confirm availability.