

#### Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Under-mount.
- Single bowl.
- Three oversized faucet holes with two oversized accessory holes to the right.
- 27" (686 mm) x 15" (381 mm)

#### **Recommended Accessories**

K- 9000 P-Trap

#### **Optional Accessories**

K- 5836 Cutting Board K- 6517 Sink Rack K- 8801 Sink Strainer

#### Components

Product includes: 1054375 Under-mount Sink Kit, 23"



### Codes/Standards

ASME A112.19.1/CSA B45.2

#### KOHLER<sup>®</sup> Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
$\bigcirc$	0	White
$\bigcirc$	FF	Sea Salt™
$\bigcirc$	96	Biscuit
$\bigcirc$	47	Almond
$\bigcirc$	FD	Cane Sugar™
$\bigcirc$	NY	Dune
$\bigcirc$	95	Ice™ Grey
$\bigcirc$	G9	Sandbar
$\bigcirc$	33	Mexican Sand™
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	20	Suede
	KA	Black 'n Tan
	FP	Caviar
	7	Black Black™




# Bakersfield<sup>™</sup>

Under-mount Kitchen Sink K-5832-5U



## Bakersfield<sup>™</sup> Under-mount Kitchen Sink K-5832-5U



#### **Technical Information**

All product dimensions are nominal.			
Bowl configuration:	Single		
Installation:	Under-mount		
Bowl area	Length: 27" (686 mm)		
	Width: 15" (381 mm)		
	Bowl depth: 8" (203 mm)		
Number of deck holes:	5		
Faucet hole(s):	2-3/8" (60 mm)		
Drain hole:	3-5/8" (92 mm)		
Template:	Under-mount, 1139754-7, required, included		

#### Notes

Install this product according to the installation guide.

Faucet holes in under-mount fixture are oversized at Ø 2-3/8" (60 mm). Drill faucet holes in counter according to fitting rough-in.

