



## PVC StarGrip® Series 4000 Restrainer

FOR USE ON IPEX BIONAX™ AWWA C909 PVCO PIPE WITH C.I. OD





## **FEATURES & BENEFITS**

- Designed for Restraining Mechanical Joint Fittings with IPEX Bionax™ ANSI/AWWA C909 PVCO Pipe.
- Castings made of Ductile Iron per ASTM A536, Grade 65-45-12.
- Maximum pressure rating includes a 2:1 safety factor
- T-Bolts/Rods/Hex Nuts: High Strength Low Alloy Steel Per ANSI/AWWA C111/A21.11
- Series 4000 Restrainer is intended for underground use only.

PRESSURE RATINGS FOR IPEX BIONAX™ AWWA C909 PVCO PIPE WITH C.I. OD			
Nominal Size	PVCO PIPE OD	Joint Restraint Maximum Pressure Rating (PSI)	T-Bolt Torque (LBFT.)
4"	4.80	150	55-65
6"	6.90	150	55-65
8"	9.05	150	55-65
10"	11.10	150	55-65
12"	13 20	150	55-65

## **NOTES**

- Installation requires T- Bolt torque values to be applied as indicated above.
- Installation to be in accordance with ANSI/AWWA C605 and ANSI/AWWA C600 with exception of T-bolt Torque (see above chart)
- Pipeline testing to be in accordance with ANSI/AWWA C605.

