



Cinch®

Under-Mount Kitchen Sink

11724-2

Features

- Integrated faucet deck prevents drilling of faucet holes in countertop surface.
- Optimized front-to-back dimension maximizes the amount of countertop material behind and in front of the sink.
- 9" (229 mm) depth provides generous workspace.
- Rear-oriented drain locations maximize usable basin space and storage space under the counter.
- SilentShield® sound-absorption technology offers quieter performance.

Material

- Premium 18-gauge stainless steel.

Recommended Products/Accessories

7400 Sink Strainer
15288 Sink Rack
15289 Sink Rack
K-23726 Drain treatment
K-23729 Stainless steel cleaner

Included Components

Product consists of:
91915 Hardware Kit




Codes/Standards

ASME A112.19.3/CSA B45.4

STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration: High-low

Installation: Under-mount

Bowl area (Left): Length: 15-1/8" (384 mm)
Width: 18-1/2" (470 mm)
Bowl depth: 9-5/16" (237 mm)
Water depth: 9-5/16" (237 mm)

Bowl area (Right): Length: 12-13/16" (325 mm)
Width: 14-7/8" (378 mm)
Bowl depth: 7-13/16" (198 mm)
Water depth: 7-13/16" (198 mm)

Number of deck holes: 2

Faucet hole spacing: 4" (102 mm)

Faucet hole(s): 1-3/8" (35 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1105667-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.