# STERLING. A KOHLER. COMPANY


#### Features

- 18-gauge stainless steel
- One-piece steel construction, no center weld
- Undermount design
- Luster finish
- Available with or without integrated faucet deck
- Offset high/low basins
- Includes SilentShield\_ $_{\ensuremath{\mathcal{B}}}$  sound-absorption technology
- 31-1/2" (800 mm) x 20-1/2" (521 mm)
- 9-5/16" (237 mm) large basin height
- 7-13/16" (198 mm) small basin height

#### **Codes/Standards Applicable**

Specified model meets or exceeds the following:

• ASME A112.19.3/CSA B45.4



## **Colors/Finishes**

• NA: None applicable

Model	Description	Faucet Holes	Colors/Finishes
11724	Kitchen sink without integrated faucet deck (shown)	• 0	
11724-1	Kitchen sink with integrated faucet deck	<b>□</b> 1	🗅 NA
11724-2	Kitchen sink with integrated faucet deck (shown)	<b>2</b>	🗆 NA

#### **Specified Model**

СІЛСНтм

**KITCHEN SINK** 

# СІЛСНтм


## **Technical Information**

Fixture*:	Large basin	Small basin		
Basin area	15-1/8″ (384 mm) x 18-1/2″ (470 mm)	12-13/16″ (325 mm) x 14-7/8″ (378 mm)		
Basin depth	9-5/16" (237 mm)	7-13/16" (198 mm)		
Drain hole	Ø 3-5/8" (92 mm)	Ø 3-5/8" (92 mm)		
Faucet hole	Ø 1-3/8" (35 mm)			
* Approximate measurements for comparison only.				

Included components:			
Hardware kit	91915		
Cut-out template	1105667-7		

#### **Installation Notes**

Install this product according to the installation guide.



**Product Diagram** 

CINCH™ KITCHEN SINK Page 2 of 2 1118491-4-**C** 

