



T5 Fluorescent T5U Series

Features

All purpose direct wire fluorescent undercabinet or display light where a compact design and low profile is required. The T5 lamp source is 1-1/4" deep and 3-5/8" wide in various lengths and is available with rocker switch and convenience outlet. Low profile applications include kitchens, study areas, displays and computer stations. Standard knockouts are located on top, back or ends for direct connection. A direct wire UL listed connector is included and is suitable for 3/8" flexible conduit or 3 wire Romex.

Construction

Housing is die-formed of 22-gauge steel. Separate hinge-able service tray allows for easy installation and is securely fastened with 2 hex nuts. Power connections are made inside service tray.

Finish

All exposed metal parts are post painted lighting grade white gloss enamel paint.

Diffuser

White acrylic diffuser with internal ribbing snap-fits into housing.

Electrical

This unit is wired with UL listed electronic residential grade normal power factor for 120V/60 Hz AC operation.

Lamping

For use with T5 linear fluorescent bi-pin lamps; not included. Models with "T" suffix; T5 linear fluorescent 4100K CW bi-pin lamps included.

Certification

Fixtures are cULus listed for damp locations and carry a UL rating for undercabinet mounting.

Options (consult factory)

High power factor ballast

Specifications and dimensions

subject to change without notice.

Ordering Information:

Standard	Lamps & Switch	Qty. Lamp	L	W	D	M
T5U108	T5U108RT	1 F8T5	12-3/8"	3-5/8"	1-1/4"	7-1/16"
T5U113	T5U113RT	1 F13T5	21-3/8"	3-5/8"	1-1/4"	16-1/16"
T5U208	T5U208RT	2 F8T5	24-3/8"	3-5/8"	1-1/4"	19-1/4"
T5U138	T5U138RT	2 (1) F13T5 & (1) F8T5	34-3/8"	3-5/8"	1-1/4"	28-7/8"
T5U213	T5U213RT	2 F13T5	42-3/8"	3-5/8"	1-1/4"	37-1/4"

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

