

# Incandescent

# Kensington

Bath & Vanity

Type \_\_\_\_\_\_


P2783 [


P2784 □

P2785

LIP	nich	
ГП	าเรท	

		Dimensions (Inches)					
Catalog No.	Forged Bronze	Lamping	<u>A</u>	<u>B</u>	<u>C</u>	<u>D</u>	
P2783	-77	1 (m) 100w	6	9-1/2	7	4-3/4	
P2784	-77	2 (m) 100w	15	9-5/8	7-5/8	6-1/2	
P2785	-77	3 (m) 100w	24-1/8	9-1/2	7-5/8	6-1/4	





# **Specifications:**

#### General

- Trumpet shaped frosted caramel swirl glass shades: 6" dia. x 5" ht.
- Scroll arms
- Mounts in "up" or "down" position
- Painted Forged Bronze (-77) finish
- Steel Construction
- Companion chandelier, foyer, pendant, and close to ceiling fixtures are available

# **Mounting**

- Wall mounted
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Oval backplate:

o P2783 is 5" width x 9" ht.

o P2784 is 9" width x 5" ht.

o P2785 is 9" width x 5" ht.

#### **Electrical**

- Medium based ceramic sockets
- Pre-wired

### **Labeling**

• UL-CUL damp location listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

www.progresslighting.com Rev. 2/10