

Incandescent

Kensington

Chandelier


Туре _____

-77

P4158 🗌

Finish

Catalog No.	Forged Bronze		Dimensions (Inches)			
		Lamping	<u>A</u>	<u>B</u>	<u>C</u>	
P4158	-77	3 (m) 100w	18	20-1/2	96	



Specifications:

General

- Trumpet shaped frosted caramel swirl glass shades: 6" dia. x 5" ht.
- Shades are in down position
- Scroll arms
- Six feet of 9 gauge matching chain supplied
- Painted Forged Bronze (-77) finish
- Steel construction
- Companion chandelier, foyer, pendant, close to ceiling and bath and vanity fixtures are available

Mounting

- Ceiling mounted on chain
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included <u>Electrical</u>
 - Medium based ceramic sockets
 - 15 feet of wire supplied
 - Pre-wired

Labeling

• UL-CUL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

www.progresslighting.com 2/10