

Submittal Data

PROJECT:	UNIT TAG:	QUANTITY:	
	TYPE OF SERVICE:		
REPRESENTATIVE:	SUBMITTED BY:	DATE:	
ENGINEER:	 APPROVED BY:	DATE:	
CONTRACTOR:	ORDER NO.:	DATE:	



UPS 43-100 SF


Circulator pumps

Product photo could vary from the actual product

Conditions of Service				
Flow:				
Head:				
Efficiency:				
Liquid:	Water			
Temperature:	68 °F			
NPSH required:				
Viscosity:				
Specific Gravity:	1.000			


Pump Data				
Maximum operating pressure:	145 psi			
Liquid temperature range:	32 230 °F			
Maximum ambient temperature:	104 °F			
Approvals:	ETL, CSA			
Type of connection:	S.S. Flange			
Flange standard:	USA Oval			
Pipe connection:	2 - Bolt Flange			
Product number:	95906639			

Motor Data				
Max. power input:	370 W			
Rated power - P2:	0.33 HP			
Rated voltage:	230 V			
Main frequency:	60 Hz			
Insulation class:	Н			
Motor protection:	Contact			
Thermal protection:	internal			





Submittal Data



Materials:

Pump housing: Stainless steel

DIN W.-Nr. 1.4301

Impeller: Composite, PES

