




## Product Specifications for E21309-10PC

Job Name:	Job Type:
Quantity:	Comments:



**E21309-10PC**  
**Inca 7-Light Pendant**



**Finish**  
Polished Chrome

**Glass/Shade**  
Clear/White

**Product Category**  
Multi-Light Pendant

### Lamping

Number of Bulb(s)	7
Light Type	Xenon
Bulb Type	G9
Max Bulb Wattage	40
Max Fixture Wattage	280
Rated Life	±2,000 Hours
Rated Lumens	±3,500
Color Temp	±2,900 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard

### Measurements

Width	15.75"
Height	10.00"
Length	N/A
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	18.00"
Max Overall Height	130.00"
Hanging Weight	8.58 lb(s)
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	130.00"
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

### Shipping

Carton Weight	12.10 lb(s)
Carton Width	19.70"
Carton Height	12.20"
Carton Length	19.70"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

### Certification

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

### Other

UPC Code	845094026815
Material	Metal

### Equivalents

Incandescent Watts	N/A
Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.