

NIBCO

1516 Middlebury Street Elkhart, IN 46516-4740

Phone: 574.295.3000 • **Fax:** 800.234.0557

E-Mail: info@nibco.com • Web site: www.nibco.com

Material Number NL95X0A, T-585-S6-R-66-LL - Two-Piece Stainless Steel Ball Valve - Full Port

The NIBCO® ball valve provides ease of operation with quarter-turn (90 degrees) open to close. The reinforced PTFE seat ring and stainless steel ball/stem exhibits high chemical resistance properties and is recommended for process piping. This valve features threaded ends for easy installation. Please refer to NIBCO technical data sheets, valve selection guides, chemical resistance guide and catalog for engineering and installation information. Choose NIBCO® ball valves for the most specified,



+ more

Specifications	-
UPC Code	039923797889
Туре	Ball Valve
Valve Size	1
Connection Type	T Female NPT Thread (FIPT)
Seal Material	RPTFE (Reinforced)
Seat Material	RPTFE (Reinforced)
Stem Material	SS - Stainless Steel
Ball Material	SS - Stainless Steel
Body Material	Stainless Steel
Cv Coefficient	36
Valve Operator	CS Locking Lever Handle

Description	T585S6R66LL 1 THD FP BV 2PT MTG LL SS
eClass Classification	Stainless Steel Ball Valves
Turns/Operation	Quarter-Turn
Weight	2.210 lb