








**SPECIFICATIONS**

	LENGTH X WIDTH X THICKNE S S		6-PACK PROD NO	25-PACK PROD NO	APPLICATION	
	TPI	IN				MM
<b>WOOD</b>	6	6 x 7/16 x .050	152 x 11 x 1.3	21063676GRC	21077B676GRC	 Scroll cutting
	6	6 x 3/4 x .050	152 x 19 x 1.3	21060666GR	21074B666GR	
	6	9 x 3/4 x .050	229 x 19 x 1.3	21062966GR	21076B966GR	
	6	12 x 3/4 x .050	305 x 19 x 1.3	21061166GR	21075B1166GR	
<b>METAL</b>	10	6 x 3/4 x .035	152 x 19 x .9	21064610GR	21078B610GR	
	10	8 x 3/4 x .050	203 x 19 x 1.3	21065810GR	21079B810GR	
	14	4 x 3/4 x .035	102 x 19 x .9	21066414GR	21080B414GR	
	14	6 x 3/4 x .035	152 x 19 x .9	21067614GR	21081B614GR	
	18	4 x 3/4 x .035	102 x 19 x .9	21068418GR	21082B418GR	
	18	6 x 3/4 x .035	152 x 19 x .9	21069618GR	21083B618GR	
	18	8 x 3/4 x .035	203 x 19 x .9	21070818GR	21084B818GR	
	24	6 x 3/4 x .035	152 x 19 x .9	21072624GR	21086B624GR	
24	8 x 3/4 x .035	203 x 19 x .9	21073824GR	21087B824GR		
<b>DEMOLITION</b>	6	6 x 7/8 x .062	152 x 22 x 1.6	210886066GR	21220B6066GR	
	6	9 x 7/8 x .062	229 x 22 x 1.6	21090966GR	21222B966GR	
	6	12 x 7/8 x .062	305 x 22 x 1.6	21091106GR	21223B106GR	
	10	9 x 7/8 x .062	229 x 22 x 1.6	21089960GR	21221B960GR	
<b>EXTREME METAL LAZER™</b>	8	6 x 1 x .042	152 x 25 x 1.1	210926108GR	21224B6108GR	
	8	9 x 1 x .042	229 x 25 x 1.1	210969108GR	21228B9108GR	
	10	6 x 1 x .042	152 x 25 x 1.1	210936110GR	21225B6110GR	
	10	9 x 1 x .042	229 x 25 x 1.1	210979110GR	21229B9110GR	
	10	12 x 1 x .042	305 x 25 x 1.1	2110012110GR	21237B12110GR	
	14	6 x 1 x .042	152 x 25 x 1.1	210946114GR	21226B6114GR	
	14	9 x 1 x .042	229 x 25 x 1.1	210989114GR	21235B9114GR	
	14	12 x 1 x .042	305 x 25 x 1.1	2110112114GR	21238B12114GR	
	18	6 x 1 x .042	152 x 25 x 1.1	210956118GR	21227B6118GR	
	18	9 x 1 x .042	229 x 25 x 1.1	210999118GR	21236B9118GR	
18	12 x 1 x .042	305 x 25 x 1.1	2110212118GR	21239B12118GR		