




Frigidaire 30" Freestanding Electric Range

Model: FFEF3011LW

29-7/8" W x 28-13/32" D x 47-3/4" H

MSRP: \$449.00

 White

Specifications

Product Code: FFEF3011LW

Product Type: Ranges

Power Type: Electric

Size: 30"

Installation Type: Free-Standing

UPC Code: 0-12505-50226-2

Color: White

Certifications & Approvals

Agency Approval: UL

Exterior Specifications

Door Finish: Metal Painted

Handle Color: White

Cooking Controls

Bake: Yes

Broil: Yes

Preheat: Integrated with Bake

Interface: Membrane

Oven Light: External Rocker Switch

Main Oven: Manual Clean

Timer: Yes

Controls: Easy-Set™

Cooktop Specifications

Cooking Surface: Upswept Coil

Right Front: 6" – 1,250 Watts

Right Rear: 8" – 2,100 Watts

Left Front: 8" – 2,100 Watts

Left Rear: 6" – 1,250 Watts

Knob Type: Plastic

Bowl Type: Chrome

Oven Specifications

Oven 1 Type: Main

Oven 1 Bake: 2,600 Watts

Oven 1 Baking System: Even Baking Technology

Oven 1 Broil : 3,000 Watts
Oven 1 Broiling System: High – Low
Oven 1 Interior Lighting: 1
Oven 1 Rack Configuration: 2 Standard
Oven 1 Interior Height: 17"
Oven 1 Interior Width: 23"
Oven 1 Interior Depth: 18-3/4"
Oven 1 Interior Color: Slate
Oven 1 Cleaning System: Manual Clean
Oven Window: Standard

Exterior Dimensions

Height: 47-3/4"
Width: 29-7/8"
Depth: 28-13/32"
Depth (to Center of Arc): 25-3/4"
Depth (with Door 90° Open): 44-5/8"

Electrical Specifications

Power Supply Connection Location: Rear Centerline
Lower
Voltage Rating: 120V / 240V or 120V / 208V, 60Hz
Connected Load (kW Rating) @ 120V:
Connected Load (kW Rating) @ 240V: 10.0 / 7.5
Minimum Circuit Required (Amps): 40A

General Specifications

Product Weight (lbs): 120
Shipping Weight (lbs): 150
