Fuzion 7260 LH Whirlpool

Product Codes beginning with: FUZ7260WCL

Also applies to products sold under part numbers: EG40, KP15, EG55, KP25, KP30, KP35, KP40, KP45

TECHNICAL SPECIFICATIONS				
	English	Metric		
Outer Dimensions	71 3/4" L x 59 3/4" W x 24" H	1822 mm L x 1518 mm W x 610 mm H		
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	49 1/2" L x 42" W x 42" W	1257 mm L x 1067 mm W x 1067 mm W		
Drain/Pump Configuration	Center drain/Left end pump	Center drain/Left end pump		
Bath Weight (empty)	207 lbs	94 kg		
Total Weight/Floor Loading	1,790 lbs 60.1 lbs/ft ²	811 kg 293 kg/m ²		
Operating Gallonage (min-max)	110 (min) 148 (max) U.S. Gals	417 (min) 561 (max) L		
Electrical Specifications	Each component requires a separate, dedicated GCFI protected circuit(s)			
Motor/Pump	120V 20A 60HZ			
Heater	120V 15A 60HZ			

FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic

Install Type: Drop-in with wood frame or Undermount Available Colors: White (W), Almond (A), Oyster (Y), Black (B) Cut-out: 70" x 58" or Undermount Template DD44000

Standard (Included) Features:

15 jets, In-line Heater, Chromatherapy lighting, infinity edge overflow, 2 neck massaging waterfalls, 2 pillows, chrome twist and turn drain (for alternate finishes, replace with standard parts, 1.5" drain elbow) **Available Control Systems:**

J4 Luxury Control Panel (standard)

J5 Luxury LCD Control Panel

Available Upgrades:

Whisper Quiet Technology, Illumatherapy Lighting

Available Accessories:


HB74 Optional wood frame (specify finish) 900: Unfinished, 935: Wenge, 936: Teak

KEY DIMENSIONS

D095 TheraPro Jet Trim Kit (specify metal finish) P556 AccuPro Jet Trim Kit (specify metal finish) 827: Chrome, 826: Brushed Nickel, 845: Oil Rubbed Bronze *Note: D095 (Chrome) is standard with Illumatherapy. GQ88 Light Chromatherapy Add-on Kit DD50 Replacement Pillow (specify color) 959: White, 958: Almond, 969: Oyster


*Faucet installation note:

Selecting a faucet for rim mounting: The combined thickness at the rim of the bathtub shell and optional wood deck is 2" (50 mm) nominal. The length of the faucet tailpiece(s) must be long enough to extend past this dimension and have ample clearance to assemble any hardware (i.e. locknut, water supply fittings, etc.) necessary for installation. For undermount units, the combined thickness of the bathtub shell is 1/2" (12 mm) nomial and the undermount deck should not exceed the length of the faucet tailpiece(s), including any assembly hardware.



Side View

Letter	Description	English	Metric		
L	Outer Length	71 3/4"	1822 mm		
W	Outer Width	59 3/4"	1518 mm		
Н	Overall Height**	24"	610 mm		
А	Overflow Height	16 3/4"	425 mm		
В	Long Edge to Drain Center	12 1/16"	306 mm		
С	Short Edge to Drain Center	36"	915 mm		
D	Drain Shoe Length	8 1/2"	216 mm		
E	Deck Height**	4"	102 mm		
F	Deck Width*	3 1/2"	89 mm		
G	Service Access Dimensions	12" H x 18" L	305 mm x 457 mm		
I	Floor Cut-out for Drain	18 1/2" x 4"	470 mm x 102 mm		
-	₩ 				





**Height of tub only, optional wood frame adds 1.25"

Drain/Overflow Note: Drain included. Non-standard installation, refer to manual.

NOTE: Graphics May Not be to Scale

© 2010 Jacuzzi Luxury Bath • For additional information call Customer Service 800-288-4002 • www.jacuzzi.com/technicalspecs Refer to installation instructions included with fixture before beginning installation. Please confirm product availability and specifications before commencing with any installation work. PRODUCT SPECIFICATIONS AND AVAILABILITY ARE SUBJECT TO CHANGE WITHOUT NOTICE. HD430

.lacvzzi