Fuzion 7260 Salon Spa Combination



Product Codes beginning with: FUZ7260CCR

Also applies to products sold under part numbers: FM25, KN55, KN60, KN65, KN70, KN75, KN80, KN85

TECHNICAL SPECIFICATIONS				
	English	Metric		
Outer Dimensions	71 3/4" L x 59 3/4" W x 24" H	1822 mm L x 1518 mm W x 610 mm H		
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	49 1/2" L x 42" W x 42" W	1257 mm L x 1067 mm W x 1067 mm W		
Drain/Equipment Configuration	Center drain/Right end pump & blower	Center drain/Right end pump & blower		
Bath Weight (empty)	242 lbs	109.8 kg		
Total Weight/Floor Loading	1,825 lbs 61.3 lbs/ft ²	828 kg 299.2 kg/m²		
Operating Gallonage (min-max)	110 (min) 148 (max) U.S. Gals	417 (min) 560 (max) L		
Electrical Specifications	Each component requires a separate, dedicated GCFI protected circuit(s)			
Motor/Pump & Heater	240V 20A 120HZ			
Blower	120V 15A 60HZ			

FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic

Install Type: Drop-in with wood frame or Undermount

Available Colors: White (W), Almond (A), Oyster (Y), Black (B)

Cut-out: 70" x 58" or Undermount Template DD44000

Standard (Included) Features:

15 jets, In-line Heater, Chromatherapy lighting,

900w blower, bottom air channels, infinity edge overflow, 2 neck massaging waterfalls, 2 pillows, chrome twist and turn drain (for alternate

finishes, replace with standard parts, 1.5" drain elbow)

Available Control Systems:

J4 Luxury Control Panel (standard)

J5 Luxury LCD Control Panel

Available Upgrades:

Whisper Quiet Technology,

Illumatherapy Lighting

Available Accessories:

HB74 Optional wood frame (specify wood) 900: Unfinished, 935: Wenge,

936: Teak

D095 TheraPro Jet Trim Kit (specify metal finish)

P556 AccuPro Jet Trim Kit (specify metal finish)

827: Chrome, 826: Brushed Nickel, 845: Oil Rubbed Bronze *Note: D095 (Chrome) is standard on Illumatherapy jets.

GQ88 Light Chromatherapy Add-on Kit


DD50 Replacement Pillow (specify color) 959: White, 958: Almond,

969: Oyster


*Faucet installation note:

Selecting a faucet for rim mounting: The combined thickness at the rim of the bathtub shell and optional wood deck is 2" (50 mm) nominal. The length of the faucet tailpiece(s) must be long enough to extend past this dimension and have ample clearance to assemble any hardware (i.e. locknut, water supply fittings, etc.) necessary for installation. For undermount units, the combined thickness of the bathtub shell is 1/2" (12 mm) nomial and the undermount deck should not exceed the length of the faucet tailpiece(s), including any assembly hardware.


KEY DIMENSIONS




*Deck width reflects only area indicated on detail



Letter	Description	English	Metric
L	Outer Length	71 3/4"	1822 mm
W	Outer Width	59 3/4"	1518 mm
Н	Overall Height**	24"	610 mm
Α	Overflow Height	16 3/4"	425 mm
В	Long Edge to Drain Center	12 1/16"	306 mm
С	Short Edge to Drain Center	36"	915 mm
D	Drain Shoe Length	8 1/2"	216 mm
E	Deck Height**	4"	102 mm
F	Deck Width*	3 1/2"	89 mm
G	Service Access Dimensions	12" H x 18" L	305 mm x 457 mm
ı	Floor Cut-out for Drain	18 1/2" x 4"	470 mm x 102 mm







Note: Drain included. Non-standard installation, refer to manual