## **Fuzion 7236 Salon Spa Combination**



Product Codes beginning with: FUZ7236CRL

Also applies to products sold under part numbers: FE05, KL55, KL60, KL65, KL70, KL75, KL80, KL85

TECHNICAL SPECIFICATIONS		
	English	Metric
Outer Dimensions	70 ¾" L x 35 ½" W x 24" H	1797 mm L x 902 mm W x 610 mm H
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	48" L x 21 ½" W x 21 ½" W	1219 mm L x 546 mm W x 546 mm W
Drain/Equipment Configuration	Right hand drain/Left end pump & blower	Right hand drain/Left end pump & blower
Bath Weight (empty)	181 lbs	82.1 kg
Total Weight/Floor Loading	1,256 lbs 72.2 lbs/ft <sup>2</sup>	570 kg 352.3 kg/m <sup>2</sup>
Operating Gallonage (min-max)	77 (min) 99 (max) U.S. Gals	291.5 (min) 375 (max) L
Electrical Specifications	Each component requires a separate, dedicated GCFI protected circuit	
Motor/Pump & Heater	240V 20A 60HZ	
Blower	120V 15A 60HZ	

## FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic

Install Type: Drop-in with wood frame or Undermount Available Colors: White (W), Almond (A), Oyster (Y), Black (B)

Cut-out: 69" x 33" or Undermount Template DD42000

Standard (Included) Features:

14 jets, In-line Heater, Chromatherapy lighting,

900w blower, bottom air channels, infinity edge overflow, 1 pillow, chrome twist and turn drain (for alternate finishes, replace with standard parts, 1.5" drain elbow)

**Available Control Systems:** 

J4 Luxury Control Panel (standard)

J5 Luxury LCD Control Panel

Available Upgrades:

Whisper Quiet Technology, Illumatherapy Lighting

Available Accessories:

HB77 Optional wood frame (specify wood) 900: Unfinished, 935: Wenge,

936: Teak

D095 TheraPro Jet Trim Kit (specify metal finish) P556 AccuPro Jet Trim Kit (specify metal finish)

827: Chrome, 826: Brushed Nickel, 845: Oil Rubbed Bronze \*Note: D095 (Chrome) is standard on Illumatherapy jets.

GQ88 Light Chromatherapy Add-on Kit

DD50 Replacement Pillow (specify color) 959: White, 958: Almond,

969: Oyster

Letter

W

## \*Faucet installation note:

Description

Outer Length

Outer Width

Selecting a faucet for rim mounting: The combined thickness at the rim of the bathtub shell and optional wood deck is 2" (50 mm) nominal. The length of the faucet tailpiece(s) must be long enough to extend past this dimension and have ample clearance to assemble any hardware (i.e. locknut, water supply fittings, etc.) necessary for installation. For undermount units, the combined thickness of the bathtub shell is 1/2" (12 mm) nomial and the undermount deck should not exceed the length of the faucet tailpiece(s), including any assembly hardware.

**English** 

70 3/4"


35 1/2"

Metric


1797 mm

902 mm


## **KEY DIMENSIONS**




\*Deck width reflects only area indicated on detail.



Н Overall Height\*\* 24" 610 mm Overflow Height 17" 432 mm Α 10 1/4" B Long Edge to Drain Center 260 mm С Short Edge to Drain Center 17 11/16" 447 mm 7" D Drain Shoe Length 178 mm 4" Ε Deck Height\*\* 102 mm Deck Width\* 76 mm G Service Access Dimensions 12" H x 18" L 305 mm x 457 mm 12" x 4" 305 mm x 102 mm Floor Cut-out for Drain





s 1.25"

Note: Drain included. Non-standard installation, refer to manual.

NOTE: Graphics May Not be to Scale

\*\*Height of tub only, optional wood frame adds 1.25

© 2011 Jacuzzi Luxury Bath • For additional information call Customer Service 800-288-4002 • www.jacuzzi.com/technicalspecs

Refer to installation instructions included with fixture before beginning installation. Please confirm product availability and specifications before commencing with any installation work.

PRODUCT SPECIFICATIONS AND AVAILABILITY ARE SUBJECT TO CHANGE WITHOUT NOTICE.

HD29000A REL 08/11