Fuzion 7260 Pure Air Bath



Product Codes beginning with: FUZ7260ACR

Also applies to products sold under part numbers: ME10, ME30

TECHNICAL SPECIFICATIONS				
	English	Metric		
Outer Dimensions	71 3/4" L x 59 3/4" W x 24" H	1822 mm L x 1518 mm W x 610 mm H		
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	49 1/2" L x 42" W x 42" W	1257 mm L x 1067 mm W x 1067 mm W		
Drain/Blower Configuration	Center drain/Right end blower	Center drain/Right end blower		
Bath Weight (empty)	200 lbs	91 kg		
Total Weight/Floor Loading	1,783 lbs 59.9 lbs/ft²	809 kg 292.3 kg/m ²		
Operating Gallonage (min-max)	70 (min) 148 (max) U.S. Gals	265 (min) 560 (max) L		
Electrical Specifications	Each component requires a separate, dedicated GCFI protected circuit(s)			
Blower	120V 15A 60HZ			
Chromatherapy (if selected)	120V 15A 60HZ			

FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic

Install Type: Drop-in with wood frame or Undermount

Available Colors: White (W), Almond (A), Oyster (Y), Black (B)

Cut-out: 70" x 58" or Undermount Template DD44000

Standard (Included) Features:

Chromatherapy lighting, 800w blower,

bottom and side air channels, infinity edge overflow, 2 pillows, chrome twist and turn drain (for alternate finishes, replace with standard parts,

1.5" drain elbow)

Available Control Systems:

J4 Luxury Control Panel (standard)

J5 Luxury LCD Control Panel

Available Upgrades:

900w blower (with J5 LCD Control Panel)

Available Accessories:

HB74 Optional wood frame (specify wood) 900: Unfinished, 935: Wenge

936: Teak

GQ88 Light Chromatherapy Add-on Kit


DD50 Replacement Pillow (specify color) 959: White, 958: Almond,

969: Oyster


*Faucet installation note:


Selecting a faucet for rim mounting: The combined thickness at the rim of the bathtub shell and optional wood deck is 2" (50 mm) nominal. The length of the faucet tailpiece(s) must be long enough to extend past this dimension and have ample clearance to assemble any hardware (i.e. locknut, water supply fittings, etc.) necessary for installation. For undermount units, the combined thickness of the bathtub shell is 1/2" (12 mm) nomial and the undermount deck should not exceed the length of the faucet tailpiece(s), including any assembly hardware.


KEY DIMENSIONS



Letter	Description	English	Metric
L	Outer Length	71 3/4"	1822 mm
W	Outer Width	59 3/4"	1518 mm
Н	Overall Height**	24"	610 mm
Α	Overflow Height	16 3/4"	425 mm
В	Long Edge to Drain Center	12 1/16"	306 mm
С	Short Edge to Drain Center	36"	915 mm
D	Drain Shoe Length	8 1/2"	216 mm
Е	Deck Height**	4"	102 mm
F	Deck Width*	3 1/2"	89 mm
G	Service Access Dimensions	12" H x 18" L	305 mm x 457 mm
1	Floor Cut-out for Drain	18 1/2" x 4"	470 mm x 102 mm







End View

**Height of tub only, optional wood frame adds 1.25"