# **Fuzion 7260 Dual Whirlpool**



Product Codes beginning with: FUZ7260WCD

Also applies to products sold under part numbers: EG70, KQ15, EG85, KQ25, KQ30, KQ35, KQ35, KQ40, KQ45

TECHNICAL SPECIFICATIONS		
	English	Metric
Outer Dimensions	71 3/4" L x 59 3/4" W x 24" H	1822 mm L x 1518 mm W x 610 mm H
Interior Dimensions (bottom of bath) L x W (Mid) x W (End)	49 1/2" L x 42" W x 42" W	1257 mm L x 1067 mm W x 1067 mm W
Drain/Pump Configuration	Center drain, Left and right pumps	Center drain, Left and right pumps
Bath Weight (empty)	242 lbs	110 kg
Total Weight/Floor Loading	1,825 lbs 61.3 lbs/ft²	829 kg 299.1 kg/m <sup>2</sup>
Operating Gallonage (min-max)	110 (min) 148 (max) U.S. Gals	417 (min) 560 (max) L
Electrical Specifications	Each zone requires a separate and dedicated GCFI-protected circuit	
Motor/Pump and Heater	Zone 1 - 240V 20A 60HZ	
Motor/Pump and Heater	Zone 2 - 240V 20A 60HZ	

# FEATURES, UPGRADES & ACCESSORIES

Material Type: High-Gloss Acrylic

Install Type: Drop-in with wood frame or Undermount

Available Colors: White (W), Almond (A), Oyster (Y), Black (B)

Cut-out: 70" x 58" or Undermount Template DD44000

Standard (Included) Features:

23 jets, In-line Heater, Chromatherapy lighting, infinity edge overflow, 2 neck massaging waterfalls, 2 pillows, chrome twist and turn drain (for alternate finishes, replace with standard parts, 1.5" drain elbow)

#### **Available Control Systems:**

J4 Luxury Control Panel (standard)
J5 Luxury LCD Control Panel

#### Available Upgrades:

Whisper Quiet Technology,

Illumatherapy Lighting

### **Available Accessories:**

HB76 Optional wood frame (specify finish) 900: Unfinished, 935: Wenge, 936: Teak

D095 TheraPro Jet Trim Kit (specify metal finish) P556 AccuPro Jet Trim Kit (specify metal finish)

827: Chrome, 826: Brushed Nickel, 845: Oil Rubbed Bronze

\*Note: D095 (Chrome) is standard on Illumatherapy jets.


GQ88 Light Chromatherapy Add-on Kit

DD50 Replacement Pillow (specify color) 959: White, 958: Almond, 969: Oyster

#### \*Faucet installation note:


Selecting a faucet for rim mounting: The combined thickness at the rim of the bathtub shell and optional wood deck is 2" (50 mm) nominal. The length of the faucet tailpiece(s) must be long enough to extend past this dimension and have ample clearance to assemble any hardware (i.e. locknut, water supply fittings, etc.) necessary for installation. For undermount units, the combined thickness of the bathtub shell is 1/2" (12 mm) nomial and the undermount deck should not exceed the length of the faucet tailpiece(s), including any assembly hardware.

## **KEY DIMENSIONS**



diffrenects offly area indicated off detail.		
į.	W	
E		
t	(Heater) (Motor)	
	Side View	

Letter Description **English** Metric Outer Length 71.75" 1822 mm W Outer Width 59.75" 1518 mm Н Overall Height\*\* 24" 610 mm Α Overflow Height 16.75" 425 mm В Long Edge to Drain Center 12 1/16" 306 mm С Short Edge to Drain Center 36" 915 mm D Drain Shoe Length 8.50" 216 mm Ε 4" Deck Height\*\* 102 mm F Deck Width\* 3.50" 89 mm Service Access Dimensions 12" H x 18" L 305 mm x 457 mm Floor Cut-out for Drain 18.50" x 4" 470 mm x 102 mm





\*Height of tub only, optional wood frame adds 1.25"

Note: Drain included. Non-standard installation, refer to manual.