

# Pre-Rinse Faucets

**TECK<sup>®</sup>**  
COMMERCIAL

**DELTA<sup>®</sup>**

## SPECIFICATION FOR 55C15\_ \_ : (EXAMPLE)

- **CAST BRASS WALLMOUNT** pre-rinse faucet
- 203 mm (8"), two handle, integral check stops
- **CER-TECK<sup>®</sup>** 1/4 turn structures
- Polished chrome-plated finish trim
- ADA compliant, color indexed, vandal resistant, 76mm (3.0") metal lever blade handles
- 3/8" IPS rigid riser, wall bracket, spray head hook and ... with ... (add No. 5 product variation) with ... (add outlet required)

## SPECIFICATION FOR 55C12\_ \_ & 55C13\_ \_ : (EXAMPLE)

- **CAST BRASS DECKMOUNT** pre-rinse faucet
- Two handle, inlet check tails
- Polished chrome-plated finish
- **CER-TECK<sup>®</sup>** 1/4 turn structures
- ADA compliant, color indexed vandal resistant, 76 mm (3.0") metal lever blade handles
- 3/8" IPS rigid riser, wall bracket, spray head hook and ... with ... (add product variation No. 2 or No. 3) with ... (add outlet required)

**55C1513**



### Engineer/Architect Approval

Model Specified:

Approval:

Date:

### MODEL NUMBER EXAMPLE:

Configurations vary, see below for availability.

**55C1583-S8**

#### Variation

- 2 = 8" (203 mm) Deckmount
- 3 = 4" (102 mm) Deckmount
- 5 = 8" (203 mm) Wallmount







#### Outlet

- 1 = Spray with spring loaded S/S hose, auto shut-off
- 8 = Same as #1 outlet, but with Add-on faucet

#### Handle

- 3 = 3" (76 mm) Hooded lever

S\* = Optional swing spout dimensions:  
S7 = 11" Tubular  
S8 = 14" Tubular

AVAILABLE MODELS 		VARIATION		
OUTLET		2 Deckmount 8" (203 mm) 	3 Deckmount 4" (102 mm) 	5 Wallmount 8" (203 mm) 
1 Spray with Spring Loaded SS Hose, Auto Shut-Off 		55C1213	55C1313	55C1513
8 Spray with Spring Loaded SS Hose, Auto Shut-Off and with Add-On Faucet (S5 Spout 8" Tubular and 1.5 gpm (5.7L/min) outlet) 		55C1283 55C1283-S8	55C1383	55C1583 55C1583-S7 55C1583-S8

Refer to [www.specselect.com](http://www.specselect.com) for individual models.

Note: Use this page front and back as a product submittal sheet.

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or [www.specselect.com](http://www.specselect.com) for finish options and product availability.


**DSP-55C** Rev. E

# Pre-Rinse Faucets

**TECK<sup>®</sup>**  
COMMERCIAL


**DELTA**

## APPROVALS:

- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- For commercial use only
-  Lever Blade Handle  
Indicates compliance to ICC/ANSI A117.1
- Verified compliant with 0.25% weighted average Pb content regulations.
- For commercial use only

(Contact Delta Representative for State and/or Local Approvals.)

## FLOW RATE vs PRESSURE



### Add-On Spout Outlet

■ Aerator

**Flowrate w/ Standard Pre-Rinse Spray Outlet**  
1.6 GPM @ 60 PSI

**Flowrate w/ Energy Saver Pre-Rinse Spray Face**  
(Also supplied with standard product)  
1.2 GPM @ 60 PSI

## PRODUCT VARIATION No. 5

**INLETS** - 1/2 - 14 NPT (Female) or 1/2 - 14 NPT (Male)  
with Supplied Nipple

## PRODUCT VARIATION No. 2 & 3

**INLETS** - 3/8 or 1/2" Flexible Riser or 1/2 - 14 NPSM  
Coupling Nut (Supplied)


## FOR OPTIONAL SWING SPOUTS

See **DSP-S/S** for detailed specification.

Note: Measurements may vary  $\pm 6\text{mm}$  (0.25")

Refer to [www.specselect.com](http://www.specselect.com) for individual models.


## THIN WALL INSTALLATION




## ADD-ON FAUCET

### MODEL No. 55C1090


(Will add 152mm (6") to overall height  
if ordered and installed separately.)




## PRODUCT VARIATION No. 2




## WALL BRACKET



## PRODUCT VARIATION No. 3



## PRODUCT VARIATION No. 5



Note: Use this page front and back as a product submittal sheet.