

Item #: **P035-077**
 Product Family Name: **Bling Bling™**
 Category: **Semi Flush**
 Certification: **3057374**
 Patents:
 Notes:

UPC Code: **844349008125**
 Finish: **Chrome**
 Category Type: **Semi Flush**



Image File Name:
 P035-077--
 1377187026.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
14		9.5	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			Yes
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight:
7		No	5.93
Canopy Width:	Canopy Height:	Canopy Length:	
5	0.88		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
3	A19 Med			
Max Bulb Wattage:	Socket:			
100	E26 Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:
16.5	7.5	16.5
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
9.17	1.182	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Perforated Steel W/Crystals
Part No.:	Quantity:
PG034-1	
Width:	Length:



Damp Location
 Yes



Title 17
 Yes



ETL Intertek
 Yes