# STEAMIST®

## Steam Generator

## Models: SM-5, SM-7, and SM-9

## **Features**

Limited lifetime warranty - 2-year in home labor warranty where available

Generator typically can be installed up to 25 ft. from the bathing area

Diagnostic LED Displays

Stainless Steel Construction

Solid-State Circuitry

## **Codes/Standards**


UL 499

**UL/CUL Listed** 

City of LA - Approved

City of New York - M.E.A. Approved

State of Mass. Approved



Steam Generator Specification Chart						
Model Number	Product Number	KW Rating	Max. Cu. Ft. Range*	Volts/Phase/ Max. Amps	Line Fuse	Dimensions L x W x H
SM-5	5010 5011	5	100	240/1/21 208/1/24	30	15" x 6" x 15.5"
SM-7	7010 7011	7	220	240/1/29 208/1/34	40	
SM-9	9010 9011	9	360	240/1/38 208/1/43	50	

Refer to sizing guidelines to accurately determine the proper size generator for the installation.

90°C copper wire is required for generator connection. Installation shall be in accordance with NEC and local electrical codes.

## Required Equipment

SMS-120, SMC-150, TC-110, TC-135, TC-125, TC-150, DSC-425, or DSP Controls

# Required Electrical Service

Dedicated circuit required: See Specification Chart for proper electrical requirements

### **Product Information**

Water Supply - 3/8" Compression Fitting, 120 PSI Max

Steam Line - 3/4" Brass BPT male thread

Pressure Relief Valve - 3/4" NPT female thread

Capped 1/2" drain line - Auto Drain Ready

#### Generator

Weight - 30 lbs.

## **Installation Notes**

Steam Generators can be typically mounted within 25 ft. of the bathing area.

Steam Generators should be accessible for service.

Do not install generators outside, in moist, humid area or in an area where parts may freeze or corrode.

Steamhead to be mounted 18" above floor or 6" above rim of tub and as far from the seating area as possible.

## **Rough-in Notes**

Access: 21" W x 18" D x 22" H (28" W with Auto Drain)

