# PF75DC & PF75FC

# **Boiler Drain**



## **Product Features**

- Max working pressure: 125 PSI
- Rated temperature: 40 ~ 160°F
- Brass body
- · Full pattern with stuffing box
- No kink 1/2" & 3/4" male IPS
- PF75DC dual inlet connection



### **Product Specifications**

Product Code	Description	Inlet Connection	Outlet Connection
PF75DC	1/2 BRS MIP BLR DRN	1/2 MIP NPT Threaded End & 1/2 SWT	3/4 MIP NH Threaded End
PF75FC	3/4 BRS MIP BLR DRN	3/4 MIP NPT Threaded End	3/4 MIP NH Threaded End

NO.	ITEM	MATERIAL TYPE
1	Wheel Nut	Steel
2	Name Plate	Aluminum
3	Hand Wheel	Aluminum
4	Stem	Cast Iron
5	Packing Nut	Brass
6	Packing	NBR
7	Bonnet	Brass
8	Washer	Non-asbestos Fibre
9	Seat	NBR
10	Seat Screw	Brass
11	Body	Brass



#### Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

#### WARNING

This product contains lead or lead compounds known to the State of California to cause cancer and birth defects and other reproductive harm. Do not use in connection with drinking water. Wash hands after handling.

