PF80DC & PF80FC




Compression Stop Valve

Product Features

- Brass body
- 125 psi
- Operating temperature: 40-160°F
- Compression connections

No.	Part Name	Material	QTY
1	Wheel Nut	V8	1
2	Name Plate	1050H18	1
3	Hand Wheel	FC20	1
4	Stem	B584-C857	1
5	Packing Nut	B16-C36000	1
6	Packing	NBR	1
7	Bonnet	B584-C857	1
8	Washer	Nylon	1
9	Seat Packing	NBR	1
10	Packing Screw C2600W		1
11	Body	B584-C857	1
12	Sleeve	Brass	2
13	Nut	Brass	2





SKU	DESCRIPTION	INLET CONNECTION	OUTLET CONNECTION	A (OPEN)		A (CLOSED)		В		
				in	mm	in	mm	in	mm	
PF	80DC	1/2 COMP ST VLV	1/2 COMPRESSION END	1/2 COMPRESSION END	3.428	87.1	3.196	99.5	2.975	75.6
PF	80FC	3/4 COMP ST VLV	3/4 COMPRESSION END	3/4 COMPRESSION END	3.664	93.1	3.373	85.7	3.517	89.3

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

WARNING: This product contains lead or lead compounds known to the State of California to cause cancer and birth defects and other reproductive harm. **Do not use in connection with drinking water. Wash hands after handling.**

