J MOEN® COMMERCIAL

Specifications

PRODUCT DESCRIPTION

- Brass construction w/chrome plated finish
- 1" IPS supply 1-1/2" top spud

OPERATION

- Adjustable sensor eyes
- Battery powered (4) standard AA (included)
- Average battery life 250,000 cycles
- Self-diagnostic electronics
- Piston flushing mechanism
- Self cleaning filter system
- Low battery indicator light

FLOW

- Operating pressures 10 to 125 psi
- 1.0 gpf (gallons per flush) up to 60 seconds/ 1.6 gpf after 60 seconds
- 24 hour sentinel flush
- Manual override button

VALVE

- 1" IPS angle stop (vandal resistant)
- Mechanical manual override button
- Adjustable installation (left or right connection)


STANDARDS

Third party certified by IAPMO to meet ASME A112.19.2M and all applicable requirements referenced therein and complies with requirements of ASSE 1037



WARRANTY

Warranted for 5 years against material or manufacture defects.



1-1/2" Battery Powered Exposed Style **Closet Flush Valve**

Model: 8310DF16

* Intended for use with matching flow rates as specified by the fixture manufacturer

