



Standard Features & Accessories

All models include

- Exclusive SureSpark™ Ignition System for all burners
- Exclusive VariSimmer[™] setting for all burners
- Removable porcelain burner bowls
- Drip tray with roller bearing glides
- Exclusive combination of single u-shaped bake burners and infrared broil burner, all with electric spark ignition
- Six functions—natural airflow bake, convection bake, infrared broil, convection infrared broil, convection dehydrate, and convection defrost
- Standard kickspace height
- Shipped standard with heavy-duty metal knobs with stainless steel finish
- Shipped with stainless steel island trim*

30"W. 4B models include

- Convection oven capacity:
 - o Overall capacity—4.0 cu. ft. (23"W. x 16-1/8"H. x 18-3/4"D.)
 - o AHAM Standard—3.7 cu. ft. (23"W. x 16-1/8"H. x 17"D.)
 - o Three heavy-duty racks/six positions o Two halogen lights
- Four 15,000 BTU stainless steel open burners with porcelain/cast iron caps and automatic ignition/re-ignition
- Center grate allows movement of cooking vessels across entire top surface

36"W. models include

- Convection oven capacity:
- o Overall capacity—5.1 cu. ft. (29"W. x 16-1/8"H.x 18-3/4"D.)
- o AHAM Standard capacity—4.6 cu. ft. (29"W. x 16-1/8"H.x 17"D.)
- o Dual bake burner

36"W. 6B models include

 Six 15,000 BTU stainless steel open burners with porcelain/cast iron caps and automatic ignition/re-ignition

COOKING

Model Options





VGIC530-4B* 30"W. Four-Burner Range





VGIC536-6B* 36"W. Six-Burner Range

FINISH DETAILS FOR ALL MODELS

- Stainless Steel (SS), Black (BK), White (WH), Metallic Silver (MS), Graphite Gray (GG), Stone Gray (SG), Taupe (TP), Biscuit (BT), Cotton White (CW), Oyster Gray (OG), Golden Mist (GM), Lemonade (LE), Sage (SA), Mint Julep (MJ), Sea Glass (SE), Iridescent Blue (IB), Viking Blue (VB), Pumpkin (PM), Racing Red (RR), Apple Red (AR), Burgundy (BU), Plum (PL), Chocolate (CH), and Cobalt Blue (CB).
 - o Finish designates door front, lower front panel, and side panels.
- Has black porcelain grates, black porcelain burner caps, black porcelain grate supports, metal knobs with stainless steel finish and black switches.
- White (WH)
 - o Finish designates door front, lower front panel, side panels, porcelain grate supports, porcelain center worktop, and knobs/switches.
 - o Has black porcelain grates and black porcelain burner caps.
- All finishes have stainless steel handle/chrome-plated brackets and stainless steel drip tray pull, control panel, and landing ledge.
- Brass Accent Option (BR)—nameplate, handle end cap, knob bezels. Brass components have a durable protective coating for maintenance-free normal use.

*Shown throughout with accessory 8" high backguard. See Installation Notes & Accessories for details.

ORDERING INSTRUCTIONS

First specify model number, and then color code (VGIC530-4BSS). If ordering optional brass accent, specify code at end (VGIC530-4BSSBR). If ordering optional LP conversion, specify code at end (VGIC530-4BSSBRLP).







Please see Installation Notes & Accessories

for important installation information including backguard, highshelf, island trim, and curb base front.



Star-K Kosher Certification for use on the Jewish Sabbath or Jewish holidays

Dimensions & Specifications


PRODUCT DIMENSIONS & DOOR SWING



VGIC530-4B* 30"W. Four-Burner Range



VGIC536-6B* 36"W. Six-Burner Range



*Add 1" to overall depth for ranges with backguards installed against a combustible wall.


	VGIC530-4B	VGIC536-6B	
Overall width	29-7/8" (75.9 cm)	35-7/8" (91.1 cm)	
Overall height	, ,	·	
Base height			
To top of side trim	35-7/8" (91.1 cm)	min. to 37" (94.0 cm) max.	
Legs adjust (with "spindles" fully extended)	1-1/8	" (2.9 cm)	
Additions to base height			
To top of island trim	Add 1	" (2.5 cm)	
To top of 8" backguard	Add 8"	' (20.3 cm)	
To top of high-shelf	Add 23-1/2" (59.7 cm)		
Overall depth* (from rear)			
To end of side panel	24-5/16	" (61.8 cm)	
To front of door	25-3/4'	′ (65.4 cm)	
To end of landing edge	28-1/16	" (72.3 cm)	
To end of door handle	28-11/16" (72.9 cm)		
*Add 1" to overall depth for ranges with backgua	rds installed against a combustible	wall.	
Oven			
Interior width	23" (58.4 cm)	29" (73.7 cm)	
Interior height	16-1/8" (41.0 cm)		
Interior depth	Overall - 18-3/4" (47.6 cm) AHAM - 17" (43.2 cm)		
Overall interior size	Overall 4.0 cu. ft.	Overall 5.1 cu. ft.	
	AHAM 3.7 cu. ft.	AHAM 4.6 cu. ft.	





COOKING

Dimensions & Specifications



Minimum clearances from adjacent combustible construction

- Cooking surface and below, i.e., 36" (91.4 cm) and below
- o Sides—0"
- o Rear—1" with backguard or highshelf; 0" with island trim and non-combustible rear wall; 6" (15.2 cm) with island trim and combustible rear wall
- o Top grate support—36" (91.4 cm)
- Above cooking surface, i.e., above 36" (91.4 cm)
- o Sides-6" (15.2 cm)
- o Within 6" (15.2 cm) side clearance, wall cabinets no deeper than 13" (33.0 cm) must be minimum 18" (45.7 cm) above cooking surface

- Wall cabinets directly above product must be minimum 42" (106.7 cm) for sealed top burners above cooking surface
- Use range only with factory supplied legs
- 1. This range may be installed directly adjacent to existing 36" (91.4 cm) high base cabinets. Important: The top grate support must be 3/8" (0.95 cm) above the adjacent base cabinet countertop. This may be accomplished by raising the unit using the adjustment spindles on the legs.
- 2. The range **cannot** be installed directly adjacent to sidewalls, tall cabinets, tall appliances, or other side vertical surfaces above 36" (91.4 cm) high.

- There must be a minimum of 6" (15.2 cm) side clearance from the range to such combustible surfaces above the 36" (91.4 cm) counter height.
- 3. Within the 6" (15.2 cm) side clearance to combustible vertical surfaces above 36" (91.4 cm), the maximum wall cabinet depth must be 13" (33.0 cm) and wall cabinets within this 6" (15.2 cm) side clearance must be 18" (45.7 cm) above the 36" (91.4 cm) high countertop.
- 4. Wall cabinets above the range must be a minimum of 42" (106.7 cm) above the range cooking surface for the full width of the range. This minimum height requirement does not apply if a rangehood is installed over the cooking surface.







UTILITY REQUIREMENTS



GAS

- Shipped natural gas standard; field convert to LP/propane with optional accessory kit or order as LP by adding LP after color code
- Accepts standard residential 1/2" ID gas service line
- Gas manifold pressure
- Natural gas 5.0" W.C.P.
- o LP/Propane 10.0" W.C.P.



ELECTRICAL

- Four-foot (121.9 cm) cord included with range
- Three-wire with ground/threeprong plug
- 120 V/60 Hz
- Maximum amp usage—30"W. 4B—0.8336"W. 6B—1.5



PLUMBINGNot applicable

Installation Requirements


ACCESS REQUIREMENTS



VGIC530-4B* 30"W. Four-Burner Range



VGIC536-6B* 36"W. Six-Burner Range





1 2

Note: Ground plug and electrical wire toward the direction of the electrical outlet.

VGIC530-4B

VGIC536-6B

15,000 BTU Nat. (4.4 kW)/ 12,500 BTU LP (3.7 kW) 15,000 BTU Nat. (4.4 kW)/ 12,500 BTU LP (3.7 kW)

Broil burner rating

Surface burner rating

Surface burners

18,000 BTU Nat. (5.3 kW)/16,000 BTU LP (4.7 kW)

Bake burner rating

30,000 BTU Nat./LP (8.8 kW)





COOKING

Installation Notes & Accessories

A backguard, high-shelf, or island trim must be used for all installations.

Island Trim

- Stainless Steel (SS)
- Coordinates with all finishes
- For island/peninsula installation
- Can replace backguard if wall is non-combustible
- Included and shipped automatically with the 30"W. and 36"W. ranges

Model	Description	Approx. ship wt. lbs. (kg)
P30TII	30"W. island trim	10 (4.5)
P36TII	36"W. island trim	11 (5.0)

8"H. Backguard

- Stainless Steel (SS)
- Coordinates with all finishes

Model	Description	Approx. ship wt. lbs. (kg)
P30BG8	30"W. backguard	14 (6.3)
P36BG8	36"W. backguard	17 (7.7)

High-shelf

- Stainless Steel (SS)
- Coordinates with all finishes
- Shelf comes attached to a 24"H. backguard

١	Model	Description	Approx. ship wt. lbs. (kg)
	B30HS24	30"W. high-shelf	45 (20.3)
	B36HS24	36"W. high-shelf	50 (22.5)

Countertop Side Trim

- Stainless Steel (SS)
- Coordinates with all finishes
- One pair of trim
- Installs on side of unit; overlaps countertop

Model	Description	Approx. ship wt. lbs. (kg)
P24CST	24"D side trim	2 (0.9)

Countertop Rear Trim

- Stainless Steel (SS)
- Coordinates with all finishes

Model	Description	Approx. ship wt. lbs. (kg)
P30CRT	30"W. countertop rear trim	2 (0.9)
P36CRT	36"W. countertop rear trim	2 (0.9)





COOKING

Installation Notes & Accessories

Curb Base Front

- Stainless Steel (SS)
- Coordinates with all finishes
- Front only
- Conceals range legs
- Completely assembled
- Easily clips onto range legs after range is installed

Custom Curb Base Front

- Remove stainless steel front and recycle
- Conceals range legs
- Attach locally supplied trim
- Completely assembled
- Easily clips onto range legs after range is installed
- Provides drop-in range look

Model	Description	Approx. ship wt. lbs. (kg)
P30CBF4	30"W. curb base front	9 (4.1)
P36CBF4	36"W. curb base front	10 (4.5)

LP/Propane Conversion Kit

Allows for field conversion of range from natural gas to LP

Model	Description	Approx. ship wt. lbs. (kg)
LPKPDR	Natural to LP/propane conversion kit	2 (0.9)

Compliance Information





WARRANTY INFORMATION*

- Three-year full warranty—complete product
- Ten-year limited warranty—porcelain oven and porcelain inner door panel
- Five-year limited warranty—surface burners, griddle burners, grill burners, and oven burner
- Ninety-day limited warranty—cosmetic parts such as glass, painted, and decorative items

^{*} For complete warranty see Use & Care Guide. Warranty valid on Viking products shipped within the United States and Canada.

