

PFW6042AV

PROFLO®

Whirlpool and Soaking Baths **60 x 42**

Product Features

- Durable easy-care acrylic construction
- Textured slip-resistant bottom
- Eight adjustable, color matched hydro jets, including two lumbar jets
- High efficiency 5.6 amp/.8 HP motor w/ 90 GPM max flow
- Heater blank, safety suction and silent air induction
- Available as an invigorating whirlpool and an un-jetted soaking bath
- Air activated on/off switch

General Specifications

- 60" length overall
- 42" width overall
- 20" overall height
- 40 gallon operating capacity
- 56 gallon total capacity to overflow
- Pre-wired for simple plug-in installation
- Requires a single 115V/20 amp GFCI circuit

Color Palette




- White – WH
- Biscuit – BS

Model Numbers

PFW6042AV	60" x 42" acrylic whirlpool
PFS6042AV	60" x 42" acrylic soaking bath
PFSK60	5' removable apron
PFSK60RP	5' removable panel apron
PFTLK	Tile flange kit
MIRPRESSHTR	Whirlpool heater



PFW6042AV



Warranty and Codes

This product features a 5-year limited warranty and meets or exceeds the following standards: Whirlpools - IAPMO PS32-84, UL listing 27E7, ANSI Z124.1-95, ASME A112.19.8M-87R(96) and ASME A112.19.7M-95. Baths - ANSI Z124.1-95. In an effort to continually improve our products, design changes may periodically be made. Ferguson reserves the right to provide newly designed material to fill any order unless otherwise agreed to in writing.

Distributed Exclusively by Ferguson and Wolseley Canada