


# 1152 1/4"-3"

**Bronze Gate Valve**  
**125 SWP - 200 WOG †**  
**Solid Wedge Disc • Rising Stem**  
**Union Bonnet • Threaded Ends**  
**Conforms to: MSS SP-80**



Note: Not intended for use in potable water.

| MATERIAL LIST |                  |            |                  |
|---------------|------------------|------------|------------------|
| No.           | PART             | MATERIAL   | SPECIFICATION    |
| 1             | Body             | Bronze     | ASTM B62         |
| 2             | Bonnet           | Bronze     | ASTM B62         |
| 3             | Wedge Disc       | Bronze     | ASTM B62         |
| 4             | Stem             | Bronze     | ASTM B62         |
| 5             | Union Bonnet Nut | Bronze     | ASTM B62         |
| 6             | Packing          | Graphite   | Commercial       |
| 7             | Gland            | Brass      | ASTM B124 C37700 |
| 8             | Packing Nut      | Brass      | ASTM B283 C37700 |
| 9             | Handwheel        | Mall. Iron | Commercial       |
| 10            | Name Plate       | Aluminum   | Commercial       |
| 11            | Handwheel Nut    | Brass      | ASTM B 16        |

| DIMENSIONS - INCHES/MILLIMETERS |       |      |       |      |                |
|---------------------------------|-------|------|-------|------|----------------|
| Units                           | Size  | A    | B     | C    | C <sub>v</sub> |
| Inches                          | 1/4   | 1.75 | 5.13  | 2.00 | 5.6            |
| mm                              |       | 45   | 130   | 51   |                |
| Inches                          | 3/8   | 1.88 | 5.13  | 2.00 | 10.7           |
| mm                              |       | 48   | 130   | 51   |                |
| Inches                          | 1/2   | 2.13 | 5.50  | 2.50 | 17.6           |
| mm                              |       | 54   | 140   | 64   |                |
| Inches                          | 3/4   | 2.25 | 6.25  | 2.75 | 32.0           |
| mm                              |       | 57   | 159   | 70   |                |
| Inches                          | 1     | 2.56 | 7.19  | 2.75 | 54.0           |
| mm                              |       | 65   | 183   | 70   |                |
| Inches                          | 1 1/4 | 2.75 | 8.56  | 3.13 | 97.0           |
| mm                              |       | 70   | 218   | 79   |                |
| Inches                          | 1 1/2 | 3.25 | 9.63  | 3.50 | 135.0          |
| mm                              |       | 83   | 245   | 89   |                |
| Inches                          | 2     | 3.63 | 11.75 | 4.00 | 230.0          |
| mm                              |       | 92   | 299   | 102  |                |
| Inches                          | 2 1/2 | 4.50 | 14.50 | 4.75 | 337.0          |
| mm                              |       | 114  | 368   | 121  |                |
| Inches                          | 3     | 4.88 | 16.75 | 5.25 | 536.0          |
| mm                              |       | 124  | 426   | 133  |                |

† Non-Shock

**INNOVATION** IN EVERY VALVE

The information presented on this sheet is correct at time of publication. Milwaukee Valve reserves the right to change design and/or materials without notice. For our Installation, Operation and Maintenance Manual and the most current product information go to [www.milwaukeevalve.com](http://www.milwaukeevalve.com). ⚠ State of California Prop 65  
**WARNING:** Cancer and Reproductive Harm. For more information visit [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov).

**MILWAUKEE VALVE**