




**E21306-10PC**  
**Inca 1-Light Pendant**

# Product Specifications for E21306-10PC

Job Name:	Job Type:
Quantity:	Comments



**Finish**  
Polished Chrome

**Glass/Shade**  
Clear/White

**Product Category**  
Mini Pendant

## Lamping

Number of Bulb(s)	1
Light Type	Xenon
Bulb Type	G9
Max Bulb Wattage	40
Max Fixture Wattage	40
Rated Life	±2,000 Hours
Rated Lumens	±800
Color Temp	±2,900 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard

## Measurements

Width	7.75"
Height	8.00"
Length	N/A
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	18.00"
Max Overall Height	130.00"
Hanging Weight	2.20 lb(s)
Height Adjustable	N/A
Slope	120°
Chain Length	N/A
Wire Length	130.00"
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

## Shipping

Carton Weight	3.08 lb(s)
Carton Width	9.80"
Carton Height	9.84"
Carton Length	9.84"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

## Certification

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

## Other

UPC Code	845094038207
Material	Metal

## Equivalents

Incandescent Watts	N/A
Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.