

# Terrazzo-Ware<sup>™</sup> Mop Sink - Standard Height (12") Series



Fixture May Show Some Available Options

Please visit www.acorneng.com for most current specifications.

## Terrazzo Standard Height Mop Sink

**Mop Sink** is an attractive, durable fixture designed to be easy to install and maintain. **ACORN Terrazzo-Ware**<sup>™</sup> precast mop sinks provide flexibility in configuration and size as required by the design of the building and the specific installation. Custom sizes and colors are also available.

**Construction** is one piece, precast terrazzo composed of marble chips cast in Portland cement to provide a compressive strength of at least 3,000 PSI seven days after casting. The mop sink surface is ground smooth and sealed to provide years of service.

**Integral Drain** is supplied with a removable, stainless steel grid strainer and provides for an inside caulked connection to a 3" pipe. The mop sink has coved corners and is pitched to the drain outlet to provide positive drainage. A beehive dome strainer is optionally available.

**Shoulders** come standard without caps exposing the natural terrazzo finish. Optionally, they may be capped with stainless steel for protection.

**Tiling Flanges** made of galvanized steel are provided loose as an easy to install accessory when flexibility and simplicity are desired. As an alternative, factory installed galvanized steel tiling flanges extending at least 1" above the shoulder can be specified.

**Accessories** to complement and complete the installation of the mop sink include:

- chrome finish faucets
- 36" hose to reduce splashing with wall hanger to support the hose
- mop hanger for easy storage of the mop over the sink
- rubber drain gaskets for easy installation of the fixture
- stainless steel wall quards to protect sensitive walls from splashing water
- tiling flanges for simple, flexible field installation

#### **GUIDE SPECIFICATION**

Provide and install an **ACORN Standard Height Mop Sink** (specify model number and options). Mop Sink shall be made of precast terrazzo to produce a compressive strength of not less than 3,000 PSI seven days after casting. All exposed surfaces shall be ground smooth and sealed. No air holes or pits shall be allowed on the finished surface. Sink shall have coved corners and be pitched to the outlet for positive drainage. Integral drain shall have a stainless steel strainer and provide for an inside caulked connection to a 3" pipe. The manufacturer will provide to the installer the necessary installation instructions.


Page #	T.MSSH	Revised: 9/16/08
--------	--------	------------------

# Terrazzo-Ware™: Mop Sink-Standard Height (12") Series

	Traile 1 1 Top Shink Starre		orgine (12 ) deried
BASE MODEL, S	IZE & TYPE	ACCESSO	RIES
☐ TSH-24	24" Square Terrazzo Standard Height	☐ KDG3	Rubber Drain Gasket for 3" Waste Pipe
☐ TSH-32	Mop Sink 32" Square Terrazzo Standard Height Mop Sink	☐ KDG32	Rubber Drain Gasket Reducer for 2" Waste Pipe
☐ TSH-36	36" Square Terrazzo Standard Height Mop Sink	☐ KF	Tiling Flange(s) (Shipped Loose)  Specify length(s):
☐ TSH-3624	36" x 24" Rectangular Terrazzo		☐ 24" Qty: ☐ 32"Qty:
	Standard Height Mop Sink		☐ 36" Qty:
SUFFIX OPTION			Faucet, Chrome Finish (H & C)
☐ - BDS ☐ - OC	Beehive Dome Strainer Optional Colors (contact factory)	☐ KH36	Hose 36" Long with Wall Hanger
☐ - SSC	Stainless Steel Cap	☐ KMH	Mop Hanger with 3 Grips
TILING FLANGE	<b>S</b> (factory installed)		on a Stainless Steel Bracket
☐ - TF1 ☐ - TF2	Tiling Flange, Rear Side Tiling Flange, Two Adjacent Sides Specify: ☐ Right & Rear ☐ Left & Rear	☐ KWG	Wall Guard (Shipped Loose)  Specify number of sides:  ☐ 1 Side ☐ 2 Sides ☐ 3 Sides
🗖 - TF3	Tiling Flange, Three Sides		Specify length(s):
			☐ 24" Qty: ☐ 32" Qty:
			☐ 36" Qty:
		☐ LB	Lint Basket/Strainer

Please visit **www.acorneng.com** for most current specifications.

MODEL	TYPE	SIZES/DIMENSIONS
NUMBER	1166	A – LENGTH
TSH-24	SQUARE	24" (610)
TSH-32	SQUARE	32" (815)
TSH-36	SQUARE	36" (915)



## TERRAZZO-WARE BACK STANDARD HEIGHT SERIES MOP SINKS

### NOTES:

- 1. Integral drain with removable grid strainer. Drain provides inside caulk connection to 3" pipe.
- 2. —TF Tiling flange. Shown for reference only.

Important: Installation instructions and current rough-in are furnished with each fixture. Do not rough in without certified dimensions.  Dimensions are subject to manufacturer's tolerance of plus or minus 1/4" and change without notice. Acorn assumes no responsibility for use of void or superseded data. © Copyright 2007 Acorn Engineering Company					
Selection Summary	Approv	Approved for Manufacturing			
Model No. & Option	Company	Title			
Quantity	Signature	Date			

Page # T.MSSH   Revised: 9/16/	Revised: 9/16/08	t T.MSS	Page #
--------------------------------	------------------	---------	--------