



Aeon Series
AELF232/432

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number

Features

Geometric sloped sided ceiling mount fixture is available in two widths, 16" and 22" and two finishes, satin aluminum or oil-rubbed bronze. It can be used in various applications including corridors, kitchens and public spaces. This product offers a lift and shift gravity retention diffuser for ceiling mounting. Fixture mounts to standard junction box (not included).

Construction

Housing is die-formed of 22-gauge steel. Standard mounting holes and hardware are included. Decorative frame assembly is .06" extruded aluminum. Power supply connections must be made inside a junction box (not included).

Finish

Back plate is finished in lighting grade white baked gloss enamel paint. Frame assembly consists of extruded satin aluminum or applied oil-rubbed bronze with clear lacquer topcoat.

Diffuser

Acrylic diffuser is .125" thick gloss white for the satin aluminum frame and linen pattern white acrylic for the oil-rubbed bronze frame.

Electrical

This unit can be ordered in the following options: with UL listed instant-start, electronic high power factor ballast; 120-277V Universal 50/60Hz AC (MV suffix).

Lamping

For use with 2-32 or 4-32 watt T8 linear fluorescent lamps; not included.


Certification

All fixtures are cULus listed for damp locations.

Options (consult factory)

Dimming
ENERGY STAR® qualified with 120V ballast

Specifications and dimensions
subject to change without notice.



Ordering Information:

Model No.	Finish	Lamps		Dimensions			Mounting
		Qty	Type	H	W	L	M
120-277V							
AELF232SAMV	Satin Aluminum	2	F32T8	4-3/8"	16"	53-3/8"	8-1/2"
AELF432SAMV	Satin Aluminum	4	F32T8	4-3/8"	22"	53-3/8"	14"
120-277V							
AELF232RBMV	Oil-Rubbed Bronze	2	F32T8	4-3/8"	16"	53-3/8"	8-1/2"
AELF432RBMV	Oil-Rubbed Bronze	4	F32T8	4-3/8"	22"	53-3/8"	14"