


TECHNICAL SPECIFICATIONS



TS-3660

MODEL NUMBER 141227

DIMENSIONS: 59 7/8" x 35 7/8" x 75 1/8" Gelcoat



Model	A	B	C	D	E
141227	59 7/8"	37 3/8"	35 7/8"	18 5/8"	8 1/4"

STANDARD FEATURES

- One-piece gelcoated fiberglass tub-shower
- Built-in top corner shelves and integrated soap dish
- Standard acrylic handle with optional metallic finishes
- 14 1/2" deep sump
- Right or left-hand drain
- Textured floor
- Bottom bathing well : 44" L x 21 3/8" W
- Optional unique features: Above-the-Floor Rough and reinforced walls

UNIQUE FEATURES

- Above-the-floor rough (AFR)

OPTIONS

- In-line heater (factory-installed)
- Pump position opposite standard position
- All walls reinforced
- Back Wall reinforcement
- Left Wall reinforcement
- Right wall reinforcement

SYSTEMS

- Homestead

DOOR SELECTION

Combine with AKER's complete shower door offering visit www.akerbymax.com

CERTIFICATIONS

AKER products adhere to one or more of the following certifications:



Project :
 Contractor :
 AKER Representative : Tel :
 Date :

TECHNICAL SPECIFICATIONS




TS-3660


MODEL NUMBER 141227

TECHNICAL DRAWINGS


STANDARD



REINFORCEMENT BACKING OPTION 20212-L Shown OPTION 20212-R Symetrical



OPTION 20212-B



All dimensions are approximate. Structure measurements must be verified against the unit to ensure proper fit.