

Compact Fluorescent

Bath Fans Energy Star Compliant


Bath Fans

Type

PV008

-09STRWB

Catalog No.	Brushed Nickel	Lamping	Capacity	Sones	Volts	Amps		
							Dimensions (Inches)	
							Α	В
PV008	-09STRWB	2 GU-24 13w (included)	70 CFM	2.5	120V	1.0	13-3/4	11



Specifications:

Trim/Grille

- · One piece steel
- · Center mount to housing
- Dimensions 13" diameter and 5-9/16" deep (Including diffuser)

Diffuser

- · Frosted glass
- · Center mounts to Trim/Grille
- Center finial matches trim finish

Housing

- Mounts to ceiling joists, or in suspended ceilings
- Can be mounted in sloped ceilings up to a 12/12 pitch
- · Galvanized steel
- 24 gage
- · Mounting brackets with keyhole slots, and holes for ceiling wires
- Removable wiring cover for easy connections
- Internal wiring plate allows either top or side hole for conduit or BX fitter
- No KO's to remove
- Tapered polymeric 4" round duct fitting for positive connection

Motor

- 120 volt, 1.0 amp, permanently lubricated
- Specially designed polymeric blower wheel Lamping and ballast
- Two, 13 watt GU24, self-ballasted compact fluorescent lamps
- 2700K CCT

Labeling

- UL/CUL listed.
- Listed for use in insulated ceilings (IC listing)
- · Energy Star Certified

Note: Product performance is rated at 0.1 in. static pressure, based on tests conducted in AMCA's state of the art test laboratory. Sones are a measure of humanly perceived loudness based on laboratory tests.



Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

Rev. 05/14