

DATE:	TYPE:	
NAME:		
PROJECT:		



Incandescent

P2901-09

Helium

Two-light Brushed Nickel bath bar with sleek, finely ribbed etched glass shades and metal studs. This design offers great versatility with installation options that include horizontal or vertical mounting on a wall, or use overhead as a ceiling fixture - all with included hardware for easy installation. Illumination pours out of Helium's heavenly form.

Category: Bath & Vanity
Finish: Brushed Nickel (plated)

Construction: Steel construction construction

Glass: Etched ribbed glass shade

Width: 20" Height: 6" Depth: 5-3/8" H/CTR: 3"

Glass: 20" Height: 6"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal or vertical mounted Mounting strap for outlet box included Back plate covers a standard 4" hexagonal recessed outlet box 7-5/8" W., 4-5/8", 7/8"	Pre-wired 6" of wire supplied 120V	Quantity: 2 75W Medium Base Medium ceramic sockets	cCSAus Damp location listed 1 year warranty Companion Bath and Vanity, Chandelier, fixtures are available