# SERENITY 13 – SERENITY SERIES

inches (mm)

66 x 38 x 26 (1675 x 965 x 660 • Fax on Demand #1320

SOAKER MODEL #AI13AIR6638FTO
AIR BATH MODEL #AI13AIR6638F



Note: This model requires a remote blower location. Please refer to the owners manual for detailed installation instructions.

## FEATURES (ALL MODELS)

- Deep bathing well
- Slip-resistant floor
- Lucite® cast acrylic surface
- Design styles from transitional to modern
- Limited lifetime warranty
- UL and IAPMO listed

## OPTIONS

- Comfort pillow: Biscuit, Black, White
- Freestanding waste & overflow: Chrome, Oil Rubbed Bronze, Polished Brass, Brushed Nickel, White

## AQUATIC ADVANTAGE

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support
- 24-hour fax-on-demand

### COLOR & TRIM OPTIONS

| Stock | Premium |
|---|---|
| Almond | Black |
| Bone | Cashmere |
| Biscuit | Mexican Sand |
| White | Red |
| | Sandbar |
| | Sterling Silver |

Note: The interior of bathing well and outside of bathing well can each be specified in a different color.

## AVAILABLE SYSTEM

### AIR BATH

- Perimeter air channel lined with antimicrobial coating
- Variable-speed, heated-air blower and automated purge-and-dry cycle and water sensors
- Electronic control with wave and pulse features
- Factory run-tested

Two Person Bath


AQUATIC
Where Inspiration Takes Shape

AQUATIC
Where Inspiration Takes Shape



# SERENITY 13

66 x 38 x 26 (1675 x 965 x 660)
inches (mm)




## FEATURES lbs (kg)

Dimensional Tolerance ± 3/8". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

| Type and Model # | Material | System | Powered By | Heater | Controls | Drain | Pkg. Wt. |
|---|---|---|---|---|---|---|---|
| Soaker #AI13AIR6638FTO | Acrylic | – | – | – | – | Center Front | 309 (140) |
| Air Bath #AI13AIR6638F | Acrylic | Air channel | Variable speed blower | Inline | Electronic | Center Front | 339 (154) |

## DIMENSIONS inches (mm)

| Width Overall / Net | Depth Overall / Net | Height Overall / Net | Skirt Height |
|---|---|---|---|
| 66 (1675) | 38 (965) | 26 (660) | – |

## SUMP DATA inches (mm)

| Capacity to Overflow gal (ltr) | Min. Operating Capacity gal (ltr) | WIDTH @ centerline | | DEPTH @ centerline | |
|---|---|---|---|---|---|
| | | Top | Bottom | Top | Bottom |
| 63 (238) | – | 57 (1445) | 42 (1065) | 29 ¼ (740) | 23 ½ (595) |

## PLUMBING DIMENSIONS inches (mm)

| A | B | Drain Diameter / Clearance |
|---|---|---|
| 3 ½ (90) | 11 (280) | 2 (50) / 7 ¼ (185) |

NOTES:
1) Where applicable, utilize cut-out templates packed with unit for deck cutouts.

2) 16 x 16 (405 x 405) minimum access required at pump/blower location(s).

## ELECTRICAL DATA

| Component | Specification | Requirement |
|---|---|---|
| Heated Blower (Air Bath) | 10.5 AMP; 120V | 15 AMP; 120V, separate circuit; Class A GFCI |

Each Serenity air bath is equipped with an air heating system to raise the temperature of the air entering the bath. This air temperature will be lower than the bathing temperature of the water, but will help reduce rapid decrease in water temperature. In addition, the air coming from the air jets will feel cool against the skin. This system does not heat the water.


# SERENITY

## PUMP/BLOWER LOCATIONS




### AIR BATH

Center Drain Models





End Drain Models





### HOTSOAK

Center Drain Models





End Drain Models





### DRIFTBATH


Center Drain Models




End Drain Models




Center Drain Models




AQUATIC
Where Inspiration Takes Shape