


Location:



SYMMONS® Canterbury™

Widespread Lavatory Faucet SLW-4512

Specification Submittal



Model Numbers

- ☐ SLW-4512 Widespread Lavatory Faucet with pop-up drain assembly

Finish Options / Modifications

Append appropriate -suffix to model number.

- ☐ -STN Satin nickel
- Polished chrome (standard finish)

Options / Modifications

Append appropriate -suffix to model number.

- ☐ -1.5 1.5 (5.7 L/min) Flow rate restrictor
- ☐ -1.0 1.0 (3.8 L/min) Flow rate restrictor
- ☐ -0.5 0.5 (1.9 L/min) Flow rate restrictor

Warranty

- Limited Lifetime - to the original end purchaser in consumer installations.
- 5 years - for commercial installations


Feature Highlights

- Two handle widespread lavatory faucet with quarter turn ceramic components.
- 8 - 16 inch centers for mounting
- Braided supply hoses
- Pop-up drain and lift rod assembly
- Aerator with 2.2 gpm flow rate (8.3 L/min)
- Metal construction, polished chrome finish

Standards / Certifications

- ASME A112.18.1/CSA B125.1
- NSF/ANSI 61
- CA Health & Safety 116875
- EPA Watersense (with 1.5 flow rate restrictor)

Dimensions Canterbury Widespread Lavatory Faucet, SLW-4512



Note: Dimensions subject to change without notice.

Symmons Industries, Inc. ■ 31 Brooks Drive ■ Braintree, MA 02184
Phone: (800) 796-6667 ■ Fax: (800) 961-9621
Website: www.symmons.com ■ Email: gethelp@symmons.com

©2014 Symmons Industries, Inc. Printed in U.S.A. ■ ZV-954 ■ Rev B ■ 101414



SYMMONS®