

Item #: **72262-189**
UPC Code: **747396078618**
Product Family Name: **Spyglass Cove**
Finish: **Chelesa Bronze™**
Category: **Wall Mount**
Category Type: **Wall Bracket**
Certification
3187291
Patents

Notes:
(1-60W T10 Shown)



Image File Name:
72262-189--
1377128844.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
12		17.5	15
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	3.7
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		7	10.5

LAMPING

No. of Bulbs:	Light Type:			
1	A19 Med			
Max Bulb Wattage:	Socket:			
100	E26 Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:
13.63	19.75	16.5
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
7.238	2.57	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Seeded Glass
Part No.:	Quantity:
G72262	1
Width:	Height:
	Length:



Wet Location

Yes



ETL Intertek

Yes