



Polyester Braided Reinforced Flexible Connectors

Features	Benefits
Outside liner: Polyester braided	Corrosion resistant
Inside liner: High Density Polyethylene (HDPE)	Eliminates chlorine taste and odor issues
Extremely flexible	Quick and easy installation
Kink resistant	Won't cut off water supply
Made in Germany	Quality manufactured and engineered
Ferguson/Wolseley exclusive	Not available anywhere else
Max operating temperature 158°F	
Operating pressure: 145 PSI	
Burst Pressure: 725 PSI	



PFXPL5S20

Installation Instructions

- For use with water in accessible locations only
- Hand tighten plus 1/4 turn. Plastic nuts are hand tighten only. Do not over tighten nuts.
- Check for leaks before leaving job site.
- Inspect regularly for general fitness and replace if damaged, corroded, or worn.
- Do not expose to corrosive chemicals.

Sink Connectors

Product Certifications

Product #	Description	cUPC	UPC	ANSI/NSF 61	AB1953	IAPMO Listed
PFXPL1F16	LF 1/2 X 1/2 FIP 16 PLYSTR SINK CONN	X	X	X	X	X
PFXPL1F20	LF 1/2 X 1/2 FIP 20 PLYSTR SINK CONN	X	X	X	X	X
PFXPL5S12	LF 3/8C X 1/2F 12 PLYSTR SINK CONN	X	X	X	X	X
PFXPL5S16	LF 3/8C X 1/2F 16 PLYSTR SINK CONN	X	X	X	X	X
PFXPL5S20	LF 3/8C X 1/2F 20 PLYSTR SINK CONN	X	X	X	X	X
PFXPL5S30	LF 3/8C X 1/2F 30 PLYSTR SINK CONN	X	X	X	X	X

Closet Connectors

Product Certifications

Product #	Description	cUPC	UPC	ANSI/NSF 61	AB1953	IAPMO Listed
PFPC7B12	3/8C X 7/8 12 PLYSTR CLST CONN	X	X	X		X
PFPC7B16	3/8C X 7/8 16 PLYSTR CLST CONN	X	X	X		X

Dishwasher Connectors

Product Certifications

Product #	Description	cUPC	UPC	ANSI/NSF 61	AB1953	IAPMO Listed
PFPD6C60ET	3/8 X 3/8 C 60 DW CONN W/ GHT ELL	X	X	X		X
PFPD6C72ET	3/8 X 3/8 C 72 DW CONN W/ GHT ELL	X	X	X		X

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.



Distributed Exclusively by Ferguson and Wolseley Canada