

COMMERCIAL-GRADE

RESIDENTIAL GAS WATER HEATERS

PROLINE® XE POWER DIRECT VENT COMMMERCIAL-GRADE RESIDENTIAL

The ProLine® XE Power Direct Vent water heaters have been engineered to maximize efficiency and deliver a greater Uniform Energy Factor (UEF).

POWER DIRECT VENT DESIGN

- Combined horizontal and vertical vent runs up to 180 equivalent feet with 4" diameter venting (ABS, PVC, CPVC and polypropylene)
- Two-pipe sealed combustion system uses outside air, eliminating problems caused by insufficient indoor ventilation
- Reduced NOx emissions comply with air quality management district regulations

ENERGY STAR® QUALIFIED

- All models (except GS6 75 YRPDTL) meet the ENERGY STAR® requirement and may also qualify for local utility and rebate programs
- Built-in heat traps on the water inlet and outlet reduce the amount of heat lost through piping
- "Environmentally-Friendly" foam insulation reduces the amount of heat loss and contributes to overall energy efficiency

SELF-CLEANING DIP TUBE

 Helps reduce lime and sediment buildup and maximizes hot water output. Made from long-lasting PEX cross-linked polymer.

HOT-SURFACE IGNITOR

 More robust and reliable than standing pilot, and reduces energy consumption.

BLUE DIAMOND® GLASS COATING

 Provides superior corrosion resistance compared to the industry-standard glasslining.

USER-FRIENDLY

- State-of-the-art electronic gas control provides more precise temperature control
- LED control light displays operation status and diagnostics information
- Built-in heat traps on the water inlet and outlet reduce the amount of heat lost through piping

ENHANCED-FLOW BRASS DRAIN VALVE

- Our residential water heaters have a solid brass, tamper resistant, enhancedflow, ball type, drain valve.
- Uses a standard female hose fitting that allows for fast and easy draining during maintenance.
- Designed for easy operation, this valve includes an integral screwdriver slot that features a ¼ turn (open/close) radius, which not only permits full straight-through water flow but also a quick and positive shut off.

CSA CERTIFIED AND ASME RATED T&P RELIEF VALVE

DESIGN-CERTIFIED BY CSA INTERNATIONAL

- Certified at 150 psi working pressure.
- Certified to ANSI Z21.10.1-CSA 4.1 or ANSI Z21.10.3-CSA 4.3 standards governing storage tank-type water heaters.

AVAILABLE IN NATURAL GAS AND PROPANE

6-YEAR LIMITED TANK AND PARTS WARRANTY











SOLID. STATE.



COMMERCIAL-GRADE

RESIDENTIAL GAS WATER HEATERS

Madal Namban	Carrian	Nominal Capacity	Storage	First Hour Rating (Gallons)	UEF	BTU Input Per Hour	Recovery @ 90°F Rise Gallon Per Hour	Dimensions in Inches							Approx.	
Model Number Ser	Series							A	В	C	D	E	F	G	Н	Shipping Weight (lb)
GS6 40 YBPDS	200	40	38	74	0.68	40,000	45	58-1/4	49-5/8	22	29-7/8	11	13-1/4	42-1/2	15-1/4	174
GS6 50 YBPDT	200	50	48	81	0.72	45,000	50	67-1/2	58-3/4	22	29-7/8	11	13-1/4	51-3/4	15-1/4	192
GS6 50 YRPDTL 5	200	50	48	118	0.73	62,000**	73	69	60-1/4	22	29-7/8	11	13-1/4	52-3/4	15-1/4	200
†GS6 75 YRPDTL	210	75	72	129	0.68	76,000	82	70-5/8	61-1/2	26	33-7/8	11	13-1/4	53	15-1/4	277

^{*}Propane model has input of 58,000 BTU/hr.

When ordering propane (LP), change "Y" to "H" in the model number (example GS6 40 YBPDSL). For side connect models, add 'L' to model number, e.g. GPDX 50L. Side connections available on YBPDS and YBPDT models.


Side connections are standard on YRPDTL models.

Natural gas models cited are series 200/210. Propane models are series 201/211. All models rated for installation at altitudes up to 10,100 ft.

†GS6 75 YRPDTL is not ENERGY STAR® qualified.


Vent Length

Model Number	Maximum Vent Length Eq. Ft.						
Model Nulliber	Ø2"	Ø3"	Ø4"				
GS6 40 YBPDS	50'	125'	180'				
GS6 50 YBPDT	50'	125'	180'				
GS6 50 YRPDTL 5	N/A	50'	125'				
GS6 75 YRPDTL 5	N/A	50'	125'				



Optional Vent Kits

Description	Part Number
2" Vent Kit- Coupling, sound suppressor	100153232
3" Vent Kit- Coupling, sound suppressor	100153234
2" Concentric Vent Kit	100112869
3" Concentric Vent Kit	100111100
Hi Ambient Kit	100191116



FOR MORE INFORMATION CONTACT: STATE WATER HEATERS 500 TENNESSEE WALTZ PARKWAY, ASHLAND CITY, TN 37015 • 800-365-0024 TOLL-FREE USA • STATEWATERHEATERS.COM