

TOOBI_{TM}

Features

- MasterClean™ spray nozzles prohibit mineral build-up for easy cleaning
- Katalyst™ Spray Technology with air induction ball joint (patent pending)
- Single-function spray with 48 individual spray nozzles
- 2.0 gallons (7.6 L) per minute maximum flow rate
- 1/2" 14 NPT connection
- Three color options included for the trim ring white, green, or black


Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.18.1/CSA B125.1
- EPA WaterSense_®







Colors/Finishes

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description		Colors/Finishes		
K-8985	Showerhead		☐ CP	☐ Other	
Recommended Accessories					
K-7397	Shower arm and flange – 7-1/2" (19.1 cm) length, 1/2" NPT	ĺ	⊒ CP	☐ Other	


Product Specification


The showerhead shall feature MasterClean spray nozzles to prohibit mineral build-up for easy cleaning. Showerhead shall feature Katalyst™ Spray Technology with air induction ball joint (patent pending). Showerhead shall have a maximum flow rate of 2.0 gallons (7.6 L) per minute. Showerhead shall be available as a single-function spray with 48 individual spray nozzles. Showerhead shall feature a 1/2" - 14 NPT connection. Showerhead shall feature three color options included for the trim ring - white, green, or black. Showerhead shall be Kohler Model K-8985-

TOOBI_{TM}

Installation Notes

Install this product according to the installation guide.





Product Diagram

