

COMMERCIAL

DESCRIPTION

- Chrome plated metal construction
- Pressure balancing cycle valve design with 1/4 turn stops
- 3 function transfer valve
- 1/2" CC connections
- Shower arm has 1/2" IPS male thread
- Contains: showerhead, hand-held shower with non-positive pause, 69" metal hose, 30" slide bar, drop ell, vacuum breaker and mounting hardware
- Slide bar is NOT DESIGNED TO BE A GRAB BAR
- Supplied with vandal resistant screws
- · Quick cleaning rubber nozzles

OPERATION

- Temperature and transfer valve both have ADA compliant lever style handles
- Handle operates counterclockwise through a 270° arc with off at 6 o'clock, and maximum hot at the 9 o'clock position. Shut off in clockwise direction
- Adjustable temperature limit stop
- Pressure balancing mechanism maintains selected discharge temperature to $\pm 2^{\circ}$
- · Transfer valve operates 3 distinct functions
- Single function spray pattern
- Easy to operate pause button (reduces the flow of water to a trickle)

FLOW

8342 (2.5gpm/9.5 lpm)

8342EP15 (1.5gpm/5.7 lpm); WaterSense® Certified

CARTRIDGE

- · 1222HD brass cartridge design in temperature control valve
- Accommodates back-to-back installations
- Ceramic disc cartridge in transfer valve
- · Brass construction with stainless steel materials


STANDARDS


 Third party certified to WaterSense® (only applies to 1.5 gpm),ASME A112.18.1/CSA B125.1 and all applicable requirements referenced therein including ASSE 1016

• ADA 🕒 for lever handle


WARRANTY

· Warranted for 5 years against material or manufacturing defects





Specifications



Three-Function Commercial Shower System

Model: 8342, 8342EP15





NOTE: This valve is not intended to be used as a shut-off valve. To prevent the potential of cross flow, check valves must be integral to the supply valve or installed in both hot and cold water supply lines.

CRITICAL DIMENSIONS

(DO NOT SCALE)