


Zurn PEX® CR - Polymer Fittings UL 1821 Listed Barb Elbow - QQPE55FX Specification Sheet

Tag			

Dimensional Data: Inches and [mm] are subject to manufacturing tolerances and change without notice. Note: Barb geometry will vary depending upon barb size.



Part	Description	'A'	'B'	'C'	יםי
QQPE55FX	1" Barb x 1" Barb Elbow	1" Barb	1" Barb	2.00" [50.8]	2.00" [50.8]

Engineering Specification: Zurn PEX® CR Polymer Elbow. The QQPE55FX elbow is used to make sharp 90° bends. Molded from Acudel®. These fittings, as a system with Zurn PEX® tube, are pressure rated at 160 PSI at 73°F, 130 PSI at 120°F (fire protection rating),100 PSI at 180°F, and 80 PSI at 200°F. These fittings are listed by NSF as complying with the following standards: NSF/ANSI Standard 14, NSF/ANSI Standard 61, ASTM F877, CSA B137.5, ASTM F2159, and UL 1821.

Accessories

___ QCLP5X ___ QCR5X 1" QickClamp® Crimp Ring 1" Copper Crimp Ring

Rev. Date: 10/8/10 C.N. No. 111810 Dwg. No. 302750 Prod. No. QQPE55FX