### Incandescent

# 6" Housing IC, Non-IC, & Air Tight

# Recessed



# Туре\_\_\_\_\_ Р87-АТ 🗌

		Dime	Dimensions (Inches)		
Catalog No.	Lamping	Α	В	С	
P87-AT	See Trim Specifications	7-7/8 Ceiling	10-3/4 9 Openin	7-1/4 g 6-7/8	
C			в —		

## Specifications:

<u>Wiring</u>

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings

<u>Construction</u>

- Housing adjusts for ceiling thickness from 1/2" to 1-1/2" thick
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Porcelain socket with nickel-plated brass screw shell
- Notched housing for chalkline alignment
- Overspray protection
- Socket can be used as a temporary work light with 'A' lamp

### Bar Hangers

- Integral nail for wood joist construction
- Integral T-bar mounting clamps
- Spans 24" T-bar suspended ceilings
- Lock to secure housing
- Captive with joist alignment tabs
- 90-degree mounting for tight spaces

### <u>Labeling</u>

- IC and Non-IC rated
- Performance tested to ASTM E283 Air Tight requirements, including IECC, CA Title 24 and Washington State Energy Codes
- UL-CUL listed for damp location and through branch wiring
- Approved for use in New York City per calendar #40330.

### <u>Lamp/Trim</u>

- Socket mounts to trim for optimum performance and consistent lamp position
- Trim-Lok<sup>®</sup> action forces trim to fit snugly against the ceiling

www.progresslighting.com Patent# 5758959

Greenville, South Carolina

Progress Lighting

29607

701 Millennium Blvd.




LED

# 6" Housing IC, Non-IC, & Air Tight w/ Quick Link Connector

# Recessed

Type \_\_\_\_\_



Incandescent



# 6" Housing IC, Non-IC, & Air Tight w/Quick Connects

# Recessed

Туре	
P87-ATQC	

# Catalog No. Lamping A B C P87-ATQC See Trim Specifications 7-7/8 10-3/4 7-1/4 Ceiling Opening 6-7/8

## Specifications:

Wiring

- Universal junction box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Knockout free Romex clamps
- 1/2" & 3/4" Knock outs for rigid or BX fittings
- Pre-Installed wire quick connects
- Thru-branch wiring for #12 90° conductors (4 in/4 out)

### <u>Construction</u>

- Housing adjusts for ceiling thickness from 1/2" to 1-1/2" thick
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)
- Galvanized steel construction
- Porcelain socket with nickel-plated brass screw shell
- Notched housing for chalkline alignment
- Pre-installed disposable plastic cap protects socket screw shell from paint overspray
- Socket can be used as a temporary work light with 'A' lamp

### <u>Bar Hangers</u>

- Integral nail for wood joist construction
- Integral snap-on T-bar mounting clip
- Span 24" T-bar for suspended ceilings
- Lock to secure housing
- Captive with joist alignment tabs
- 90-degree mounting for tight spaces

### Labeling

- IC and Non-IC rated
- Performance tested to ASTM E283 Air Tight requirements, including IECC, CA Title 24 and Washington State Energy Codes
- UL-CUL listed for damp location and through branch wiring
- Approved for use in New York City per calendar #40330.

### Lamp/Trim

- Socket mounts to trim for optimum performance, and provides consistent vertical lamp position
- Trim-Lok<sup>®</sup> action forces trim to fit snugly against the ceiling

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607