

D5534XLFI

Product: Dishwasher
Size: XL (ADA height compliant)
Mode of installation: Integrated

Programs

Daily wash
Heavy wash
Delicate wash
Quick wash
Super quick
Eco wash
Rinse & Dry
Rinse and hold

Options

Delayed start: 24 h
High temperature
Long dry

Cleaning systems

7
Self cleaning filters
AquaLevel™ Sensor

Drying system

Turbo Drying™

Comfort/Easy of use

Fault indication
Rinse-aid indication
Time remaining indicator

Safety

AquaSafe™
SteamSafe™
KidLock™ - lock the door

Baskets

Upper: Premium
Lower: Exclusive



General

Display type: LED display
Number of programs: 9
Noise level: 48 dB(A)
Number of baskets: 2
Max loading height upper basket: 9 1/16 (230 mm)
Max loading height lower basket: 12 3/16 (310 mm)

Dimensions and installation

Height: 32 1/4 (819 mm)
Width: 23 5/8 (600 mm)
Depth: 22 7/8 (581 mm)
Length inlet hose: 66 1/8 (1680 mm)
Length outlet hose: 41 3/4 (1060 mm)
Cord length: 46 7/16 (1180 mm)
Weight net: 108 lbs
Weight gross: 112 lbs

Technical information

Connection rating: 1300 W
Current: 15 A
Voltage: 120 V

Consumption

Wash performance: A
Estimated yearly energy consumption: 231 kWh
Energy consumption/cycle: 1,07 kWh

D5534XLFI


XL DISHWASHERS (ADA COMPLIANT) - PANEL READY

UNIT DIMENSIONS

	U.S.	Metric
Height (Adjustable)*	32-1/4" to 34"	819 mm to 864 mm
Width	23-5/8"	600 mm
Depth (Includes high loop)	22-7/8"	581 mm
Depth w/Door Open	48-3/8"	1229 mm
Weight	108 lb	49 kg

TECHNICAL DATA

Electricity	120V, 60Hz, 15 amp
Water pressure	4.2 - 140 psi, 0.03-1.0 MPa, 0.3-10 Bar
Heating element	1200 watt
Max loading	1300 watt



PREPARING THE LOCATION

CUTOUT DIMENSIONS


	U.S.	Metric
Height*	32-1/4" to 34"	819 to 864 mm
Width	23-5/8" to 24"	600 mm to 610 mm
Depth	24"	610 mm

The best place for your dishwasher is in the kitchen near the sink. This makes it easier to connect the water and drain supply lines.

A built-in dishwasher must be enclosed on the top, both sides and the back.

The power-supply receptacle for the appliance shall be installed in a cabinet or on a wall adjacent to the undercounter space in which the appliance is to be installed.

The electrical and water supplies should enter through the area indicated by the shading on the illustration at right. Preferably, they should come through the right side of the machine. The access hole must be round and smooth and no bigger than 1-1/2" (38 mm) in diameter. If the partition is metal, it needs to be covered with an edge protector. Use caution when the appliance is installed or removed, to reduce the likelihood of damage to the power-supply cord.



* 32-1/4" (819 mm) height requires removal of top trim, and lowering side trim (2).

PANEL DIMENSIONS

	U.S.	Metric
4" Toe kick		
Height	30-1/8"	765 mm
Width	23-7/8"	606 mm
6" Toe kick		
Height	28-1/8"	714 mm
Width	23-7/8"	606 mm