

ASKO Classic Dishwasher



## D5434XXL W/B/S

Type: Built-in  
Colors: White, Black or TouchProof™  
stainless steel

### PERFORMANCE

Capacity: 14 place settings  
Noise level 48 dB(A)  
7Spray™ system  
PowerZone™ Pots & Pans,  
PowerZone™ Cutlery

### PROGRAMS

Daily	Heavy
Normal	Eco
Quick	Rinse & hold

### FEATURES

6 Temperatures, Turbo drying™,  
Delayed start 1-24h

### FLEXIRACKS™

Premium upper rack  
Exclusive lower rack  
Cutlery basket



MADE IN  
SWEDEN



reddot design award  
winner 2011

Asko Appliances, Inc  
PO BOX 940609 • Plano • Texas • 75094  
Phone 800.898.1879  
[www.askousa.com](http://www.askousa.com)

Art. no. 6301705

# XXL TALL TANK MODELS

## PLANNING & DESIGN: XXL DISHWASHERS


D5434XXL, D5624XXL, D5634XXLHS, D5654XXLHS, D5894XXLHS

### Unit Dimensions

	US	METRIC
HEIGHT:	34 <sup>3</sup> / <sub>8</sub> " – 36 <sup>1</sup> / <sub>2</sub> "	873 – 927 mm
WIDTH:	24"	610 mm
DEPTH:	22 <sup>7</sup> / <sub>8</sub> "	581 mm
DEPTH W/ HANDLE (HS):	24 <sup>7</sup> / <sub>8</sub> "	632 mm
DEPTH W/DOOR OPEN:	49 <sup>1</sup> / <sub>2</sub> "	1257 mm
WEIGHT:	106 lbs	48 kg

### Technical Data

Electricity	120 V, 60 Hz, 15 Amp
Water pressure	18 – 176 psi
Heating element	1200 watt
Max loading	1300 watt



### Cutout Dimensions

	US	METRIC
HEIGHT:	34 <sup>3</sup> / <sub>8</sub> " – 36 <sup>1</sup> / <sub>2</sub> "	873 – 927 mm
WIDTH:	24"	610 mm
DEPTH:	24"	610 mm

The electrical and water supplies should enter through the area indicated by the shaded area. Preferably, they should come through the right side of the machine. The access hole must be round and smooth and no bigger than 1 <sup>1</sup>/<sub>2</sub>" (38 mm) in diameter.

\* Total height can be reduced by <sup>1</sup>/<sub>2</sub>" by removing upper trim.

