



aquatherm NPT TRANSITION PIECE (male)

With hex-shaped threaded transition



Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	SW	Weight
		[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0621308	(½" — 20 mm) x ½" M	0.79	0.50	2.62	2.05	1.52	0.87	0.23
0621310	(½" — 20 mm) x ¾" M	0.79	0.75	2.66	2.09	1.52	0.94	0.28
0621312	(¾" — 25 mm) x ¾" M	0.98	0.75	2.66	2.03	1.52	0.94	0.23
0621314	(1" — 32 mm) x 1" M	1.26	1.00	3.09	2.38	2.09	1.18	0.48
0621316	(1" — 32 mm) x 1 ¼" M	1.26	1.25	3.19	2.48	2.68	1.61	0.70
0621317	(1 ¼" — 40 mm) x 1" M	1.57	1.00	3.19	2.38	2.05	1.18	0.49
0621318	(1 ¼" — 40 mm) x 1 ¼" M	1.57	1.25	3.33	2.52	2.68	1.61	0.71
0621319	(1 ½" — 50 mm) x 1 ¼" M	1.97	1.25	3.37	2.44	2.68	1.61	0.77
0621320	(1 ½" — 50 mm) x 1 ½" M	1.97	1.50	3.48	2.56	2.91	1.81	0.94
0621321	(2" — 63 mm) x 1 ½" M	2.48	1.50	3.72	2.64	2.85	1.81	1.03
0621322	(2" — 63 mm) x 2" M	2.48	2.00	4.04	2.95	3.31	1.97	1.51
0621323	(2 ½" — 75 mm) x 2" M	2.95	2.00	4.02	2.83	3.31	1.97	1.61
0621324	(2 ½" — 75 mm) x 2 ½" M	2.95	2.50	4.13	2.95	3.94	2.56	2.14
0621325	(3" — 90 mm) x 3" M	3.54	3.00	4.76	3.46	4.72	3.35	2.92
0621327	(3 ½" — 110 mm) x 4" M	4.33	4.00	5.83	4.37	5.79	4.13	6.02

aquatherm TRANSITION ELBOW (female)



Stainless steel part no. (ISO)	Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	l1	z1	D1	Weight
			[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0923008	0623008	(½" — 20 mm) x ¾" F	0.79	0.75	1.46	0.89	1.34	1.46	0.94	1.73	0.22
0923010	0623010	(½" — 20 mm) x ½" F	0.79	0.50	1.24	0.67	1.16	1.24	0.73	1.46	0.17
0923012	0623012	(¾" — 25 mm) x ¾" F	0.98	0.75	1.46	0.83	1.34	1.46	0.94	1.73	0.22
0923014	0623014	(¾" — 25 mm) x ½" F	0.98	0.50	1.34	0.71	1.34	1.46	0.94	1.46	0.17
0923016	0623016	(1" — 32 mm) x ¾" F	1.26	0.75	1.08	0.37	1.69	2.01	1.50	1.73	0.23
(NPT)											
1123018	0623018	(1" — 32 mm) x 1" F	1.26	1.00	1.34	0.63	1.69	2.62	1.75	2.37	0.55