



Measurements:

<u>Height</u> <u>Width</u> 18.50" 8.00"

Max OAH

64.00"

Hanging WeightCanopy WidthCanopy HeightCanopy Length2.42 lb5.50"1.25"5.50"

Lamping:

Incandescent MB 1,150 Rated Lumens
1.00 60W MB Color Temperature
60 total watt 2,500 Rated Life

Dimmable: Standard

Shipping:

Carton WeightCarton WidthCarton HeightCarton Length5.28 lb11.42"8.66"17.72"

 Master Pack Qty
 UPC
 UPS

 1.0000
 783209091696
 Yes

Finish:

Polished Chrome PC

Glass:

Satin White SW

Material:

Steel

Certification:

Dry Location

Additional:

MB (Not Included) Slope: 120

