


# Specifications



# Two-Handle Kitchen Faucet

Models: 87302 series

NOTE: THIS FAUCET IS DESIGNED TO BE INSTALLED THRU 4 HOLES 1-1/4" (32MM) MIN. DIA.

# **FAUCET DESCRIPTION**

- Metal construction with various finishes identified by suffix
- · Includes hose and Protégé side spray

## **OPERATION**

- Lever style handles
- Hot sidé counter-clockwise to open (clockwise to close)
- Cold side clockwise to open (counter-clockwise to close)

#### **FLOW**

Aerator is limited to 2.2. gpm (8.3 L/min) at 60 psi

## **CARTRIDGE**


- 1224 cartridge design
- Nonmetallic and stainless steel material

## **STANDARDS**

- Third party certified to meet ASME A112.18/CSA B-125.1 and all applicable requirements referenced therein
- Contains no more than 0.25% weighted average lead content
- Certified to NSF 61/9
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA 🕒 for lever handles

## **WARRANTY**

- Lifetime limited warranty against leaks, drips and finish defects to the original consumer purchaser
- 5 year warranty if used in commercial installations



# **CRITICAL DIMENSIONS**

(DO NOT SCALE)