# PFW0100,200 series



# W&O Bath Drain - Brass

## **Product Features**

- Fits most tubs 14" to 16" high
- 1-1/2" Brass tubing in 17 GA
- Adjustable self-retaining rubber head gasket
- Pre-adjustable linkage
- Brass head tee and toe
- Cast brass shoe plug
- Extra long plunger stroke
- Lubricated cast brass plunger
- Include both plastic and brass washers
- Include brass retainer strap



#### PFW0200

✔ For Submittal		Description	Dimensions										
			A		В		C		D		Gauge	Style	Finish
			in	mm	in	mm	in	mm	in	mm			
	PFW0100	W&O Bath Drain-Brass	5-13/16"~6-5/8"	147.6-168.2	4-1/16"	103.19	11-1/2"- 14"	292.1-355.6	1-1/2"	38.1	17 GA	Lift & Turn	Chrome
	PFW0200	W&O Bath Drain-Brass	5-13/16"~6-5/8"	147.6-168.2	4-1/16"	103.19	11-1/2"- 14"	292.1-355.6	1-1/2"	38.1	17 GA	Trip Lever	Chrome
	PFW0101	W&O Bath Drain-Brass	6-13/16"~7-5/8"	173.0-193.6	4-1/16"	103.19	11-1/2"- 14"	292.1-355.6	1-1/2"	38.1	17 GA	Lift & Turn	Chrome
	PFW0201	W&O Bath Drain-Brass	6-13/16"~7-5/8"	173.0-193.6	4-1/16"	103.19	11-1/2"- 14"	292.1-355.6	1-1/2"	38.1	17 GA	Trip Lever	Chrome

### **Optional trim kits**


- For Trip Lever Style

PFW0210 - BN Finish

PFW0215- ORB Finish

- For Lift & Turn Style

PFW0505 - CP Finish





### Warranty and Codes

This PROFLO product carries a 1-year limited warranty.