



Telephone: 1-519-595-4444 - Toll Free: 1-800-561-3164

Fax: 1-519-595-4380 - www.boshart.com

# HS SERIES "HEAVY DUTY" HEAT SHRINK KITS

"HS" Series heavy wall adhesive lined, flexible cross-linked polyolefin heat shrinkable tubing. DESIGNED FOR THE NEW SMALLER O.D. LEAD WIRES being used on submersible pump motors. This tubing is suitable for applications up to 600 volts providing excellent waterproof insulating and environmental sealing protection for splices, connections and jacket repairs. High impact and abrasion resistance of THIS HEAVY WALL TUBING PROVIDES THE HIGHEST LEVEL OF MECHANICAL DURABILITY. When heated above 120°C (250°F) there is a 3:1 shrink ratio. Tubing will shrink unrestricted to 33% of its original diameter, the recovered wall thickness of the tubing is proportional to the degree of recovery (approx. 0.08" /2mm when fully recovered)

NOTE: Due to the substantial wall thickness, the "HS" Series of Tubing takes longer to shrink to its fully recovered state (approx. 45-50 seconds). Time will vary depending on job site conditions and the heat source that is used.

Tube specs. - expanded I.D. = 0.40" min. recovered I.D. = 0.15" max. nominal wall thickness = 0.08".

| BLACK<br>KIT<br>PART NO. | CLEAR<br>KIT<br>PART NO. | WIRE<br>SIZE<br>RANGE | NO. OF<br>BUTT<br>CONN. | NO. OF<br>SHRINK<br>TUBES | TUBE<br>LENGTH | QTY<br>CASE | LIST<br>PRICE-A |
|--------------------------|--------------------------|-----------------------|-------------------------|---------------------------|----------------|-------------|-----------------|
| HS-2                     | HSC-2                    | 14,12,10              | 2 (#14 - #10)           | 2                         | 3"             | 100         | 1.80            |
| HS-3                     | HSC-3                    | 14,12,10              | 3 (#14 - #10)           | 3                         | 3"             | 100         | 2.56            |
| HS-3-4                   | HSC-3-4                  | 14,12,10              | 4 (#14 - #10)           | 3                         | 3"             | 100         | 2.79            |
| HS-4                     | HSC-4                    | 14,12,10              | 4 (#14 - #10)           | 4                         | 3"             | 100         | 3.31            |
| ONTARIO                  | #8 AWG G                 | ROUND                 | WIRE REGULAT            | ION KITS                  |                |             |                 |

| HS-4/8  | 14,12,10 | 3 (#14-10) & 1 (#8) | 4 | 3" | 50  | 3.62 |
|---------|----------|---------------------|---|----|-----|------|
| HSC-4/8 | 14,12,10 | 3 (#14-10) & 1 (#8) | 4 | 3" | 100 | 3.60 |

# #8 AWG AND #6 AWG PUMP CABLE KITS- BLACK

| Tube specs | expanded I.D. $= 0.51$ " | min. recovered I.D. $= 0.16$ | o" max. no | minal wall th | ickness = | = 0.09" |
|------------|--------------------------|------------------------------|------------|---------------|-----------|---------|
| HS8-3      | #8 AWG                   | 2 (#8) & 1 (#14 - #10)       | 3          | 4"            | 10        | 7.27    |
| HS8-4      | #8 AWG                   | 3 (#8) & 1 (#14 - #10)       | 4          | 4"            | 40        | 9.31    |
| HS6-3      | #6 AWG                   | 2 (#6) & 1 (#8)              | 3          | 4"            | 10        | 8.55    |
| HS6-4      | #6 AWG                   | 3 (#6) & 1 (#8)              | 4          | 4"            | 10        | 11.35   |

#### DELUXE - X-TRA LONG STAKON (BUTT CONN) FOR DOUBLE CRIMPING NOTE: THE HEAT SHRINK TUBING IS SAME AS IN THE KITS ABOVE

| HS8-3XLS | #8 AWG | 2 (#8) & 1 (#14 - #10) | 3 | 4" | 10 | 13.72 |
|----------|--------|------------------------|---|----|----|-------|
| HS8-4XLS | #8 AWG | 3 (#8) & 1 (#14 - #10) | 4 | 4" | 10 | 19.12 |
| HS6-3XLS | #6 AWG | 2 (#6) & 1 (#8)        | 3 | 4" | 10 | 18.37 |
| HS6-4XLS | #6 AWG | 3 (#6) & 1 (#8)        | 4 | 4" | 10 | 24.36 |

# #4 AWG AND #2 AWG PUMP CABLE KITS - BLACK

| Tube specs | expanded I.D. = 0.75" | min. recovered I.D. = 0.24 | ' max. | nominal wall | thickness | = 0.09" |
|------------|-----------------------|----------------------------|--------|--------------|-----------|---------|
| HS4-4      | #4 AWG                | 3 (#4) & 1 (#6)            | 4      | 4.8"         | 10        | 15.80   |
| DELUXE     |                       | , , , ,                    |        |              |           |         |
| HS4-4XLS   | #4 AWG                | 3 (#4) & 1 (#6)            | 4      | 4.8"         | 10        | 29.24   |



9-1

April 23/12

|    | OVERALL LENGTH |          |  |  |  |  |  |  |  |
|----|----------------|----------|--|--|--|--|--|--|--|
|    | DELUXE         | STANDARD |  |  |  |  |  |  |  |
| #8 | 1.973          | 0.835    |  |  |  |  |  |  |  |
| #6 | 2.37           | 1.015    |  |  |  |  |  |  |  |
| #4 | 2.36           | 1.142    |  |  |  |  |  |  |  |
| #2 | 2.60           | 1.272    |  |  |  |  |  |  |  |



# #8 AWG, #6 AWG, #4 AWG AND #2 AWG PUMP CABLE KITS - CLEAR

Tube specs. - expanded I.D. = 0.75" min. recovered I.D. = 0.22" max. nominal wall thickness = 0.08"

| BLACK<br>KIT<br>PART NO. | CLEAR<br>KIT<br>PART NO. | WIRE<br>SIZE<br>RANGE | NO. OF<br>BUTT<br>CONN. | NO. OF<br>SHRINK<br>TUBES | TUBE<br>LENGTH | QTY<br>CASE | LIST<br>PRICE-A |
|--------------------------|--------------------------|-----------------------|-------------------------|---------------------------|----------------|-------------|-----------------|
|                          | HSC8-4                   | #8 AWG                | 3 (#8) & 1 (#14 - #10)  | 4                         | 4"             | 10          | 9.76            |
|                          | HSC6-4                   | #6 AWG                | 3 (#6) & 1 (#8)         | 4                         | 4"             | 10          | 11.67           |
|                          | HSC4-4                   | #4 AWG                | 3 (#4) & 1 (#6)         | 4                         | 4.8"           | 10          | 14.36           |

### DELUXE - X-TRA LONG STAKON (BUTT CONN) FOR DOUBLE CRIMPING NOTE: THE HEAT SHRINK TUBING IS SAME AS IN THE KITS ABOVE

| HSC8-4XLS | #8 AWG | 3 (#8) & 1 (#14 - #10) | 4 | 4"   | 10 | 19.44 |
|-----------|--------|------------------------|---|------|----|-------|
| HSC6-4XLS | #6 AWG | 3 (#6) & 1 (#8)        | 4 | 4"   | 10 | 24.68 |
| HSC4-4XLS | #4 AWG | 3 (#4) & 1 (#6)        | 4 | 4.8" | 10 | 27.77 |

Telephone: 1-519-595-4444 - Toll Free: 1-800-561-3164

Fax: 1-519-595-4380 - www.boshart.com



April 23/12

### STAKON CONNECTORS

| PART<br>NO. | WIRE<br>SIZE | LENGTH OF<br>CONNECT | DESCRIPTION  | QUA<br>BAG | NTITY<br>CASE | LIST<br>PRICE-A |
|-------------|--------------|----------------------|--------------|------------|---------------|-----------------|
| SC-14-10    | #14-10       |                      | Bulk Stakons | 25         | 500           | 0.33            |
| SC-8        | 8            | 0.835                | Bulk Stakons | 10         | 200           | 0.73            |
| SC-6        | 6            | 1.015                | Bulk Stakons | 10         | 200           | 1.30            |
| SC-4        | 4            | 1.142                | Bulk Stakons | 4          | 200           | 2.83            |
| SC-2        | 2            | 1.272                | Bulk Stakons | 4          | 100           | 3.65            |
| DELUXE      |              |                      |              |            |               |                 |
| SC-8XLS     | 8            | 1.973                | Bulk Stakons | 10         | 200           | 5.09            |
| SC-6XLS     | 6            | 2.370                | Bulk Stakons | 10         | 200           | 5.87            |
| SC-4XLS     | 4            | 2.360                | Bulk Stakons | 4          | 200           | 7.03            |
| SC-2XLS     | 2            | 2.600                | Bulk Stakons | 4          | 100           | 8.75            |
|             |              |                      |              |            |               |                 |



# HSK SERIES "FAST RECOVERY" HEAT SHRINK KITS

"HSK" Series adhesive lined cross-linked polyolefin heat shrinkable tubing is designed for applications up to 600 volts, and provides excellent sealing protection for splices, connections, and jacket repairs. The good abrasion resistance characteristics of this tubing provide excellent mechanical protection. When heated above  $120^{\circ}\text{C}$  ( $250^{\circ}\text{F}$ ) the tubing SHRINKS RAPIDLY TO A SKIN TIGHT FIT, forcing the melted adhesive to flow forming a flexible bond. Upon cooling the adhesive solidifies, forming a permanent, non-drying flexible and waterproof barrier DESIGNED FOR THE NEW SMALLER O.D. LEAD WIRES being used on submersible pump motors. With a 4:1 shrink ratio the tubing shrinks unrestricted to 25% of its original diameter. The recovered wall thickness of the tubing is proportional to the degree of recovery (approx. 0.043" /1.1 mm when fully recovered). NOTE: This tubing will shrink to its fully recovered diameter in 25-30 seconds. Time will vary depending on job site conditions and the heat source that is used. Tube specs. - expanded I.D. = 0.45" min. recovered I.D. = 0.102" max. nominal wall thickness = 0.043".

| BLACK<br>KIT<br>PART NO. | CLEAR<br>KIT<br>PART NO. | WIRE<br>SIZE<br>RANGE | NO. OF<br>BUTT<br>CONN. | NO. OF<br>SHRINK<br>TUBES | TUBE<br>LENGTH | QTY<br>CASE | LIST<br>PRICE-A |
|--------------------------|--------------------------|-----------------------|-------------------------|---------------------------|----------------|-------------|-----------------|
| HSKB-2                   | HSKC-2                   | 14,12,10              | 2 (#14 - #10)           | 2                         | 3"             | 100         | 1.58            |
| HSKB-3                   | HSKC-3                   | 14,12,10              | 3 (#14 - #10)           | 3                         | 3"             | 100         | 2.23            |
| HSKB-3-4                 | HSKC-3-4                 | 14,12,10              | 4 (#14 - #10)           | 3                         | 3"             | 100         | 2.47            |
| HSKB-4                   | HSKC-4                   | 14,12,10              | 4 (#14 - #10)           | 4                         | 3"             | 100         | 2.88            |
|                          | * HSKC-12                | 14,12,10              | 12 (#14 - #10)          | 12                        | 3"             |             |                 |



**NOTE**: Black tubing is flame retardant. However, due to the removal of the carbon content to produce transparent tubing, the clear tubing is not flame retardant.

Larger Diameter Tubing and Butt Splice Connectors Sold Separately

### 3" LONG HEAT SHRINK TUBES - CLEAR & BLACK

Bulk packed tubes, for tubing specifications refer to the information printed with the splice kits on previous page.

| PART<br>NO.           | COLOUR       | WIRE<br>SIZE | EXPANDED<br>ID (MIN) | RECOVERED<br>ID (MAX) | WALL     | TUBING<br>LENGTH | QTY<br>CASE | LIST<br>PRICE-A |
|-----------------------|--------------|--------------|----------------------|-----------------------|----------|------------------|-------------|-----------------|
| † HST-HS-3-BK         | Black        | 14-10        | 0.40 in              | 0.15 in               | 0.08 in  | 3"               | 25          | 0.84 /3" pc     |
| † HST-HS-3-CL         | Clear        | 14-10        | 0.40 in              | 0.15 in               | 0.08 in  | 3"               | 25          | 0.84 /3" pc     |
| †† HST-HSK-3-BK       | Black        | 14-10        | 0.45 in              | 0.102 in              | 0.043 in | 3"               | 25          | 0.71 /3" pc     |
| † Used in "HS" Series | Heavy Duty K | its          | †† Used in "HSK"     | Series Fast Recove    | ry Kits  |                  |             |                 |

# 48" LONG HEAT SHRINK TUBES - BLACK

This heavy wall, adhesive lined 3:1 shrink ratio, cross-linked polyolefin heat shrinkable tubing has high impact and abrasion resistance, and provides excellent insulating/sealing protection for splices, connections and jacket repairs.

# 48" LONG HEAT SHRINK TUBES - CLEAR

This clear wall, adhesive lined, 3:1 shrink ratio, cross-linked polyolefin heat shrinkable tubing allows for visual inspection of splices. It has high impact and abrasion resistance, and provides excellent insulating/sealing protection for splices, connections, and jacket repairs.



<sup>\*</sup> The 12 pack contains 12 heat shrink tubes and 12 stakon connectors and are packaged in a resealable zip lock bag.