

Riverby® Top-mount Kitchen Sink K-5872-4A1

Features

- 25-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Top-mount.
- Three faucet holes with one accessory hole to the right.
- 25" (635 mm) x 22" (559 mm)

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K- 6194 Utility Rack with Soaking Cup K- 6239 Colander with Cutting Board

K- 6246 Cutting Board

K- 8801 Sink Strainer

Components

Product includes:

K- 6238 Sink Rack

1054375 Under-mount Sink Kit, 23"



Codes/Standards

ASME A112.19.1/CSA B45.2

KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes


Color tiles intended for reference only.


Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	47	Almond
	FD	Cane Sugar™
	95	Ice™ Grey
	G9	Sandbar
	K4	Cashmere
	20	Suede
	KA	Black 'n Tan
	7	Black Black™





Riverby® Top-mount Kitchen Sink K-5872-4A1





Technical Information

All product dimensions are nominal.

Bowl configuration: Single Installation: Top-mount


Bowl area (Only) Length: 22-1/4" (565 mm)

Width: 15-13/16" (402 mm) Bowl depth: 9" (229 mm)

Number of deck holes: 4

Faucet hole(s): 1-3/8" (35 mm)
Drain hole: 3-7/8" (98 mm)

Template: Top-mount, 1172565-7, required, included



Notes

Install this product according to the installation guide.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4-KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.

IMPORTANT! Use of the colander, wood cutting board, and utility rack requires the "reveal" cutout

option on the cutout template.

